

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

2014

© COPYRIGHT 2014

BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

LOC -

DIST -

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
NC		NEW RELEASE PER E.O. PI8793	31MAR2005	-	RDR
A		REVISED PER ECO-14-013476	04SEP2014	PV	DM



5 MATERIAL:  
CONNECTOR: PA66  
PINS: COPPER ALLOY

4 ORIENTATION OF THE "DEUTSCH" AND "-P031" TO BE OPTIONAL.

3 MAXIMUM CURRENT RATING FOR THE 3 PIN BUSBAR IS 13 AMPS.

2 BORDERS SIGNIFY THAT PINS 1, 11, 12 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 2, 3, 10 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 4, 8, 9 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR. PINS 5, 6, 7 ARE BUSSED TOGETHER WITH A 3 PIN BUSBAR.

1 THIS RECEPTACLE MATES WITH DT06-12SX-XXXX PLUG  
( X= A, B, C, D KEYS; XXXX= ALL MODIFICATIONS)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRAVEENA, V 21AUG2014	 TE Connectivity				
DIMENSIONS: INCHES [mm]		CHK R. MESSENGER 22AUG2014					
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 04SEP2014					
		PRODUCT SPEC -	NAME DT 12 WAY RECEPTACLE (4) 3 PIN BUSBARS GOLD PLATED				
MATERIAL 5		FINISH -	APPLICATION SPEC -	SIZE A3	CAGE CODE -	DRAWING NO DT04-12PX-P031	RESTRICTED TO -
CUSTOMER DRAWING			WEIGHT 26 g	SCALE 2:1	SHEET 1	OF 2	REV A

1470-19 (3/11)

THIS DRAWING IS UNPUBLISHED  
 © COPYRIGHT 2014 BY TE CONNECTIVITY  
 RELEASED FOR PUBLICATION 2014  
 ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

D

D

C


C

B


B

A


A




**DT04-12PA-P031**  
**COLOR: GREY**



**DT04-12PB-P031**  
**COLOR: BLACK**



**DT04-12PC-P031**  
**COLOR: GREEN**



**DT04-12PD-P031**  
**COLOR: BROWN**

NOTES: SEE SHEET ONE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PRAVEENA.V 21AUG2014																
DIMENSIONS: INCHES [mm]		CHK R. MESSENGER 22AUG2014																
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 04SEP2014	NAME DT 12 WAY RECEPTACLE (4) 3 PIN BUSBARS GOLD PLATED															
<table border="0"> <tr><td>0 PLC</td><td>±-</td></tr> <tr><td>1 PLC</td><td>±-</td></tr> <tr><td>2 PLC</td><td>±-</td></tr> <tr><td>3 PLC</td><td>±.020 [0.51]</td></tr> <tr><td>4 PLC</td><td>±-</td></tr> <tr><td>ANGLES</td><td>±0° 30' 0"</td></tr> </table>		0 PLC	±-	1 PLC	±-	2 PLC	±-	3 PLC	±.020 [0.51]	4 PLC	±-	ANGLES	±0° 30' 0"	PRODUCT SPEC -	SIZE A3	CAGE CODE -	DRAWING NO DT04-12PX-P031	RESTRICTED TO -
0 PLC	±-																	
1 PLC	±-																	
2 PLC	±-																	
3 PLC	±.020 [0.51]																	
4 PLC	±-																	
ANGLES	±0° 30' 0"																	
MATERIAL -		FINISH -	APPLICATION SPEC -	WEIGHT 26 g	SCALE 2:1	SHEET 2 OF 2	REV A											
CUSTOMER DRAWING																		