

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 1998 BY TE CONNECTIVITY

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	NC	NEW RELEASE PER E.O PI5871	22DEC1998	-	RDR
	A	REVISED PER E.O. PI6126	01JUN1999	-	RDR
	AI	REVISED PER PCN-23-183138	28JUL2023	MK	IG

1.758
[44.65]

.973
[24.71]

.832
[21.14]

5 MATERIAL:

HOUSING AND SHORT CAP: PA66 GF15, BLACK
 GROMMET: VMQ, ORANGE-RED
 CONTACTS: COPPER ALLOY, GOLD PLATED
 WEDGELOCK: PBT GF30, BLUE

4. THIS RECEPTACLE MATES WITH THE DT06-3S-XXXX PLUG (XXXX=J1939 MODIFICATIONS)
 CONSULT FACTORY FOR MODIFICATIONS. INCLUDED LOCKING WEDGE IS KEYPED
 TO PREVENT MISMATING AND MAY NOT MATE WITH ALL 3-WAY DT SERIES PLUGS.

3. FOR CONTACT AND WIRE SPECIFICATIONS SEE CUSTOMER DRAWING
 0425-015-0000 AND 0425-017-0000.

2. RESISTOR CHARACTERISTICS: 120 OHMS \pm 10 PERCENT, 0.4 WATTS MIN.

1. RESISTOR INSERTED INTO CAVITIES 'A' AND 'B'.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
in [mm]

MATERIAL

5

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	\pm
1 PLC	\pm
2 PLC	\pm
3 PLC	\pm .025 [0.64]
4 PLC	\pm
ANGLES	\pm 1°
FINISH	

DWN S. THEIS 21DEC1998

CHK S. BEARD 22DEC1998

APVD R. READ 22DEC1998

PRODUCT SPEC

108-151009

APPLICATION SPEC

0425-017-0000

WEIGHT 12.78 g

CUSTOMER DRAWING

TE INTERNAL PN	DEUTSCH PN	PN REV
DT04-3P-EPI0	DT04-3P-EPI0	A

NAME
 3 WAY RECEPTACLE
 WITH TERMINATING RESISTOR, EPI0 MOD
 DT SERIES

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	4AFU8	DT04-3P-EPI0	

SCALE	SHEET	OF	REV
2:1	1	1	AI

1470-19 (3/13)