



| P | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|---|-----|---------------|-----------|-----|------|
|   | B   | ECR-20-017666 | 29DEC2020 | GK  | MN   |

### LABEL AND LINER DESIGN





### PRESENTATION



| DESCRIPTION  | TEPN        | MATERIAL DESCRIPTION | TTDS     | WEIGHT (g) | ROLL DIAMETER (mm) ± 10 | ROLL DIAMETER (Inch) ± 0.393 |
|--------------|-------------|----------------------|----------|------------|-------------------------|------------------------------|
| EET-0619P-4  | 5-1768017-2 | YELLOW POLYESTER     | TTDS-174 | 0.015      | 106.78                  | 4.20                         |
| EET-0619P-8A | 5-1768017-3 | SILVER POLYESTER     | TTDS-175 | 0.012      | 106.78                  | 4.20                         |
| EET-0619P-9  | 5-1768017-4 | WHITE POLYESTER      | TTDS-177 | 0.011      | 104.77                  | 4.12                         |
| EET-0619PY-9 | 5-1768017-5 | WHITE POLYETHYLENE   | TTDS-178 | 0.013      | 111.25                  | 4.38                         |

**INSIDE WOUND  
LABEL ACROSS: 4  
PER ROLL QTY: 10000**

|               |                |
|---------------|----------------|
| ADHESIVE TYPE | PERMANENT      |
| LINER         | GLASSINE PAPER |

|                      |              |  |  |   |  |   |  |
|----------------------|--------------|--|--|---|--|---|--|
| TOLERANCES mm [INCH] |              | THIS DRAWING IS A CONTROLLED DOCUMENT.   |  | DWN 29DEC2020<br>GOPALAKRISHNA HV   |  |  TE Connectivity |  |
| LABEL HEIGHT:        | ±0.3 [.012]  | DIMENSIONS: mm [INCHES]<br> |  | CHK 29DEC2020<br>MIKE NUTTALL   |  |   |  |
| LABEL WIDTH:         | ±0.3 [.012]  |  |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± - |  | APVD 29DEC2020<br>MIKE NUTTALL  |  |
| WEB WIDTH:           | ±0.8 [.031]  | MATERIAL   |  |   |  | PRODUCT SPEC  |  |
| VERTICAL REPEAT:     | ±0.8 [.031]* | SEE TABLE  |  | APPLICATION SPEC  |  | CAGE CODE   |  |
| HORIZONTAL REPEAT:   | ±0.8 [.031]* | SEE TABLE  |  | WEIGHT  |  | DRAWING NO  |  |
| PRINT POSITIONING:   | ±0.8 [.031]* | SEE TABLE  |  | CUSTOMER DRAWING  |  | RESTRICTED TO   |  |
| LEFT MARGIN:         | ±0.4 [.016]  | FINISH   |  | SCALE   |  | SHEET   |  |
| QUANTITY:            | -0 % +2 %    | -  |  | NTS   |  | 1 OF 1  |  |
| *NON ACCUMULATING    |              |  |  | REV   |  | B   |  |