



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	29DEC2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	WEIGHT (g)	ROLL DIAMETER (mm) ± 10	ROLL DIAMETER (Inch) ± 0.393
EET-1555P-4	5-1768018-7	YELLOW POLYESTER	TTDS-174	0.101	153.53	6.04
EET-1555P-8A	5-1768018-8	SILVER POLYESTER	TTDS-175	0.080	153.53	6.04
EET-1555P-9	5-1768018-9	WHITE POLYESTER	TTDS-177	0.077	148.17	5.83
EET-1555PY-9	6-1768018-0	WHITE POLYETHYLENE	TTDS-178	0.091	165.13	6.50

**INSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 5000**

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

<p>TOLERANCES mm [INCH]</p> <table border="1"> <tr><td>LABEL HEIGHT:</td><td>±0.3 [.012]</td></tr> <tr><td>LABEL WIDTH:</td><td>±0.3 [.012]</td></tr> <tr><td>WEB WIDTH:</td><td>±0.8 [.031]</td></tr> <tr><td>VERTICAL REPEAT:</td><td>±0.8 [.031]*</td></tr> <tr><td>HORIZONTAL REPEAT:</td><td>±0.8 [.031]*</td></tr> <tr><td>PRINT POSITIONING:</td><td>±0.8 [.031]*</td></tr> <tr><td>LEFT MARGIN:</td><td>±0.4 [.016]</td></tr> <tr><td>QUANTITY:</td><td>-0 % +2 %</td></tr> </table> <p>*NON ACCUMULATING</p>		LABEL HEIGHT:	±0.3 [.012]	LABEL WIDTH:	±0.3 [.012]	WEB WIDTH:	±0.8 [.031]	VERTICAL REPEAT:	±0.8 [.031]*	HORIZONTAL REPEAT:	±0.8 [.031]*	PRINT POSITIONING:	±0.8 [.031]*	LEFT MARGIN:	±0.4 [.016]	QUANTITY:	-0 % +2 %	<p>THIS DRAWING IS A CONTROLLED DOCUMENT.</p> <p>DIMENSIONS: mm [INCHES]</p> <p>TOLERANCES UNLESS OTHERWISE SPECIFIED:</p> <table border="1"> <tr><td>0 PLC</td><td>± -</td></tr> <tr><td>1 PLC</td><td>± -</td></tr> <tr><td>2 PLC</td><td>± -</td></tr> <tr><td>3 PLC</td><td>± -</td></tr> <tr><td>4 PLC</td><td>± -</td></tr> <tr><td>ANGLES</td><td>± -</td></tr> </table> <p>FINISH -</p>		0 PLC	± -	1 PLC	± -	2 PLC	± -	3 PLC	± -	4 PLC	± -	ANGLES	± -	<p>DWN 29DEC2020 GOPALAKRISHNA HV</p> <p>CHK 29DEC2020 MIKE NUTTALL</p> <p>APVD 29DEC2020 MIKE NUTTALL</p> <p>PRODUCT SPEC SEE TABLE</p> <p>APPLICATION SPEC -</p> <p>WEIGHT SEE TABLE</p> <p>CUSTOMER DRAWING</p>		<p>NAME EET LABELS 15.00mm x 55.00mm</p> <p>SIZE A3</p> <p>CAGE CODE C2290</p> <p>DRAWING NO EET-1555</p> <p>RESTRICTED TO -</p>		<p>SCALE NTS</p> <p>SHEET 1 OF 1</p> <p>REV B</p>	
LABEL HEIGHT:	±0.3 [.012]																																				
LABEL WIDTH:	±0.3 [.012]																																				
WEB WIDTH:	±0.8 [.031]																																				
VERTICAL REPEAT:	±0.8 [.031]*																																				
HORIZONTAL REPEAT:	±0.8 [.031]*																																				
PRINT POSITIONING:	±0.8 [.031]*																																				
LEFT MARGIN:	±0.4 [.016]																																				
QUANTITY:	-0 % +2 %																																				
0 PLC	± -																																				
1 PLC	± -																																				
2 PLC	± -																																				
3 PLC	± -																																				
4 PLC	± -																																				
ANGLES	± -																																				