



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	29DEC2020	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	WEIGHT (g)	ROLL DIAMETER (mm) ± 10	ROLL DIAMETER (Inch) ± 0.393
EET-1938P-4	6-1768018-1	YELLOW POLYESTER	TTDS-174	0.089	115.55	4.55
EET-1938P-8A	6-1768018-2	SILVER POLYESTER	TTDS-175	0.071	115.55	4.55
EET-1938P-9	6-1768018-3	WHITE POLYESTER	TTDS-177	0.068	112.89	4.44
EET-1938PY-9	6-1768018-4	WHITE POLYETHYLENE	TTDS-178	0.080	121.49	4.78
EET-1938V-8A	6-1768018-5	SILVER FLEXIBLE PVC	TTDS-PV330	0.082	115.59	4.55
EET-1938V-9	6-1768018-6	WHITE FLEXIBLE PVC	TTDS-207	0.098	117.25	4.62

**INSIDE WOUND
LABEL ACROSS: 2
PER ROLL QTY: 3000**

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29DEC2020 GOPALAKRISHNA HV		STE TE Connectivity	
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES]		CHK 29DEC2020 MIKE NUTTALL			
LABEL WIDTH:	±0.3 [.012]			TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 29DEC2020 MIKE NUTTALL	
WEB WIDTH:	±0.8 [.031]	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		NAME		EET LABELS 19.05mm x 38.10mm	
VERTICAL REPEAT:	±0.8 [.031]*			PRODUCT SPEC		-	
HORIZONTAL REPEAT:	±0.8 [.031]*	MATERIAL		APPLICATION SPEC		-	
PRINT POSITIONING:	±0.8 [.031]*	SEE TABLE		-		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
LEFT MARGIN:	±0.4 [.016]	FINISH		-		A3 C2290 C-EET-1938	
QUANTITY:	-0 % +2 %	-		WEIGHT		-	
*NON ACCUMULATING		-		SEE TABLE		SCALE NTS SHEET 1 OF 1 REV B	
				CUSTOMER DRAWING			