



REVISIONS				
P	LTR	DESCRIPTION	DATE	BYN APPD
A		INITIAL RELEASE	14MAR2023	YB SL

LABEL AND LINER DESIGN



PRESENTATION



QTY PER ROLL: 3,000
 LABELS ACROSS: 2
 INSIDE WOUND

TE PN: 6-1768018-5

All dimensions in mm [INCHES]

MATERIAL	SILVER POLYVINYLCHLORID
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	KRAFT WHITE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DATE		BYN APPD	
DMN	Y. BONNINO	14MAR2023			
CHK	Y. BONNINO	14MAR2023			
APVD	S. LAZRAK	14MAR2023			
PRODUCT SPEC		NAME		EET-1938V-8A	
APPLICATION SPEC		SIZE		A2	
WEIGHT		QAGE CODE		C=6-1768018-5	
CUSTOMER DRAWING		DRAWING NO		RESTRICTED TO	
		SCALE		NTS	
		SHEET		1 of 1	
		REV		A	

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [0.02]
LABEL WIDTH:	±0.3 [0.02]
LINER WIDTH:	±0.07 [0.01]
VERTICAL REPEAT:	±0.8 [0.03]*
HORIZONTAL REPEAT:	±0.8 [0.03]*
PRINT POSITIONING:	±0.8 [0.03]*
LEFT MARGIN:	±0.4 [0.08]
QUANTITY:	-0% +2%
*NON ACCUMULATING	

DIMENSIONS:		TOLERANCES (UNLESS OTHERWISE SPECIFIED):	
mm [INCHES]		0 PLG	±
		1 PLG	±
		2 PLG	±
		3 PLG	±
		4 PLG	±
		ANGLES	±
		FINISH	-
MATERIAL		SEE TABLE	