



LABEL AND LINER DESIGN



PRESENTATION



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-20-017666	29DEC2020	GK	MN

DESCRIPTION	TEPN	MATERIAL DESCRIPTION	TTDS	WEIGHT (g)	ROLL DIAMETER (mm) ± 10	ROLL DIAMETER (Inch) ± 0.393
EET-3460P-4	9-1768018-4	YELLOW POLYESTER	TTDS-174	0.249	156.20	6.15
EET-3460P-8A	9-1768018-5	SILVER POLYESTER	TTDS-175	0.198	156.20	6.15
EET-3460P-9	9-1768018-6	WHITE POLYESTER	TTDS-177	0.191	150.67	5.93
EET-3460PY-9	9-1768018-7	WHITE POLYETHYLENE	TTDS-178	0.226	168.16	6.62
EET-3460V-4-W	9-1768018-8	WARNING YELLOW FLEXIBLE PVC	TTDS-184	0.225	157.75	6.21
EET-3460V-8A	9-1768018-9	SILVER FLEXIBLE PVC	TTDS-PV330	0.229	156.20	6.15

**INSIDE WOUND
LABEL ACROSS: 1
PER ROLL QTY: 2500**

ADHESIVE TYPE	PERMANENT
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29DEC2020 GOPALAKRISHNA HV	STE TE Connectivity
LABEL HEIGHT:	±0.3 [.012]	DIMENSIONS: mm [INCHES]		CHK 29DEC2020 MIKE NUTTALL	
LABEL WIDTH:	±0.3 [.012]			TOLERANCES UNLESS OTHERWISE SPECIFIED:	
WEB WIDTH:	±0.8 [.031]			NAME EET LABELS 34.00mm x 60.00mm	
VERTICAL REPEAT:	±0.8 [.031]*			0 PLC ± -	PRODUCT SPEC SEE TABLE
HORIZONTAL REPEAT:	±0.8 [.031]*	1 PLC ± -	2 PLC ± -	APPLICATION SPEC -	
PRINT POSITIONING:	±0.8 [.031]*	3 PLC ± -	4 PLC ± -	SIZE A3	
LEFT MARGIN:	±0.4 [.016]	ANGLES ± -	FINISH ± -	CAGE CODE C2290	
QUANTITY:	-0 % +2 %	MATERIAL SEE TABLE		DRAWING NO EET-3460	
*NON ACCUMULATING				RESTRICTED TO -	
				WEIGHT SEE TABLE	SCALE NTS
				CUSTOMER DRAWING	SHEET 1 OF 1
					REV B