


While TE Connectivity (TE) has made every reasonable effort to ensure the accuracy of the information in this catalog, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.



Technical Data

Highest Voltage U_m	kV	52
Lightning Impulse Voltage	kV	250
Length (approx.)	mm	1350
Kit Weight (approx.)	kg	10.5
Max. Conductor Size Cu/Al (approx.)	mm ²	1200
Outer Diameter Cable Insulation	mm	≤86
Outer Diameter Cable Oversheath	mm	≤100

INLINE JOINT
52 kV
HEAT SHRINKABLE
FOR XLPE – CABLE

EHVS-52H-1
Offer drawing



TE Connectivity Ltd.

Raychem High Voltage Cable Accessories

TYCO DRAWING NO.:
EPD-204-1871-00

SHEET 1 OF 1
REV C