

REV. C  
DCO 300855


TOLERANCES  $\pm .010"$  - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C	CURRENT: 100mA MAX.
RESISTANCE _____	
NOMINAL VOLTAGE _____	28 VAC - 50/400Hz
MUST OPERATE _____	16.0 VAC MAX., 50/400Hz
MUST RELEASE _____	7.5 VAC MAX., 2.0 VAC MIN., 50/400 Hz

ENVIRONMENT:	
VIBRATION _____ 33 _____ Hz TO _____ 3000 _____ Hz @ _____ 30 _____ g's	
SHOCK _____ 200 _____ g's _____ 6 _____ MS. DURATION	
TEMPERATURE _____ -70 _____ °C TO _____ +125 _____ °C	

NOTES: OPERATE TIME 15 mS MAX.
RELEASE TIME 50 mS MAX.
CONTACT BOUNCE 1 mS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: _____
10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE.
100,000 OPERATIONS

DR. B.D. 07MAR2008 | CK. J.M.B. 5/14/08

**Tyco Electronics** ©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CUST. _____ CATALOG ITEM _____	TE NUMBER _____
CUST. NO. _____ REV. _____	1617752-8

CII PART NUMBER  
FCA-210-CY7