

REV. C  
DCO 300853


TOLERANCES  $\pm .010$ " - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C  
~~RESISTANCE~~ \_\_\_\_\_ CURRENT: 30mA MAX.  
 NOMINAL VOLTAGE \_\_\_\_\_ 115 VAC - 50/400Hz  
 MUST OPERATE \_\_\_\_\_ 70.0 VAC MAX., 50/400Hz  
 \_\_\_\_\_  
 MUST RELEASE \_\_\_\_\_ 25.0 VAC MAX., 8.0 VAC MIN., 50/400 Hz  
 \_\_\_\_\_

ENVIRONMENT:  
 VIBRATION \_\_\_\_\_ 33 \_\_\_\_\_ Hz TO \_\_\_\_\_ 3000 \_\_\_\_\_ Hz @ \_\_\_\_\_ 30 \_\_\_\_\_ g's  
 SHOCK \_\_\_\_\_ 200 \_\_\_\_\_ g's \_\_\_\_\_ 6 \_\_\_\_\_ MS. DURATION  
 TEMPERATURE \_\_\_\_\_ -70 \_\_\_\_\_ °C TO \_\_\_\_\_ +125 \_\_\_\_\_ °C

NOTES: OPERATE TIME 20 MS MAX.  
 \_\_\_\_\_  
 RELEASE TIME 50 MS MAX.  
 \_\_\_\_\_  
 CONTACT BOUNCE 1 MS MAX.  
 \_\_\_\_\_

CUSTOMER DATA SHEET



CONTACT RATING: \_\_\_\_\_  
 25 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE  
 50,000 OPERATIONS

DR. B.D. 10APR2008 | CK. J.M.B. 5/14/08

**Tyco Electronics** ©COPYRIGHT 2005  
 TYCO ELECTRONICS CORPORATION  
 ALL INTERNATIONAL RIGHTS RESERVED

CUST. \_\_\_\_\_ CATALOG \_\_\_\_\_  
 CUST. NO. \_\_\_\_\_ REV. N/A

TE NUMBER  
 6-1617753-7

CII PART NUMBER  
 FCA-325-CY9