

BLUE BEAD

REV. A  
DCO 300859


TOLERANCES  $\pm .010$ " - UNLESS  
OTHERWISE SPECIFIED

COIL: @ 25°C  
RESISTANCE \_\_\_\_\_ 290 OHMS  $\pm 10\%$   
NOMINAL VOLTAGE \_\_\_\_\_ 28 VDC  
MUST OPERATE \_\_\_\_\_ 13.5 VDC MAX.  
COIL TRANSIENT SUPPRESSION: 42 VDC MAX.  
MUST RELEASE \_\_\_\_\_ 5.5 VDC MAX., 2.3 VDC MIN.

ENVIRONMENT:  
VIBRATION \_\_\_\_\_ 10 Hz TO \_\_\_\_\_ 3000 Hz @ \_\_\_\_\_ 30 g's  
SHOCK \_\_\_\_\_ 200 g's \_\_\_\_\_ 6 MS. DURATION  
TEMPERATURE \_\_\_\_\_ -70 °C TO \_\_\_\_\_ +125 °C

NOTES: OPERATE, RELEASE 15 MS MAX.  
CONTACT BOUNCE 1 MS MAX.  
CONTACT BREAK BOUNCE 0.1 MS MAX.

### CUSTOMER DATA SHEET



CONTACT RATING: \_\_\_\_\_  
10 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE  
100,000 OPERATIONS

DR. B.D. 16MAY2008 CK. J.M.B. 5/19/08

**Tyco Electronics**

©COPYRIGHT 2005  
TYCO ELECTRONICS CORPORATION  
ALL INTERNATIONAL RIGHTS RESERVED

CUST. \_\_\_\_\_ CATALOG ITEM  
CUST. NO. \_\_\_\_\_ REV. \_\_\_\_\_

TE NUMBER  
8-1617755-9

CII PART NUMBER  
FCA-410-BY4