

REV. B
DCO 300825

TOLERANCES $\pm .010"$ - UNLESS OTHERWISE SPECIFIED

COIL: @ 25°C
 RESISTANCE 78 OHMS $\pm 10\%$
 NOMINAL VOLTAGE 12 VDC
 MUST OPERATE 6.6 VDC MAX.
TRANSIENT SUPPRESSION - 42 VDC MAX.
 MUST RELEASE 3.3 VDC MAX., 0.75 VDC MIN.


ENVIRONMENT:
 VIBRATION 70 Hz TO 3000 Hz @ 30 g's
 SHOCK 200 g's 6 MS. DURATION
 TEMPERATURE -70 °C TO +125 °C

NOTES: OPERATE, RELEASE 6 MS MAX.
CONTACT STABILIZATION 2.5 MS MAX.
CONTACT BOUNCE 1 MS MAX.
CONTACT BREAK BOUNCE 0.1 MS MAX.

CUST. M83536/6-012M
 CUST. NO. ---- REV. ---

TE NUMBER
7-1617760-4

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL
5 AMPS 28 VDC, 115 VAC 400 Hz RESISTIVE
100,000 OPERATIONS

DR. B.D. 25APR2008 | CK. 5/9/08 J.M.B.

Tyco Electronics ©COPYRIGHT 2005
 TYCO ELECTRONICS CORPORATION
 ALL INTERNATIONAL RIGHTS RESERVED

CII PART NUMBER
FCB-405-0612M