

MSD INC.

ENGINEERING DATA SHEET


RELAY TYPE: FCB-405-CY4 | COMPUTER PART No.: 9364506

TEST PROCEDURE
MSDP-791

CUSTOMER/SPECIFICATION: CATALOG ITEM | REV N/A

TEST REQUIREMENTS

COIL RES.: $\pm 10\%$ 400 OHMS OPERATE TIME: 6ms MAX RELEASE TIME: 6ms MAX
 CONTACT MAKE BOUNCE: 1ms MAX. N.O. BREAK BOUNCE: 0.1ms MAX
 CONTACT STABILIZATION TIME: N/A RATED COIL VOLTAGE: 28Vdc
 CONTACT RES.: MFG TEST: 0.40 OHMS @ 10mA-6Vdc FINAL TEST: 0.50 OHMS @ 10mA-6Vdc
 CONTACT VOLTAGE DROP: FINAL TEST: .100V MAX @ 5A-6Vdc
 HI-POT: 1000 Vrms ALL POINTS
 INSULATION RESISTANCE: 100 MEGOHMS MIN @ 500 Vdc
 VIBRATION: N/A
 SEAL TEST: 1×10^{-8} MAX LEAK RATE COIL TRANSIENT SUPPRESSION: 42 Vdc MAX
 OTHER: _____



Prepared By: Date		Approved By: Date	
LES WYNNE 3-19-96		<i>J. [Signature]</i> 3-20-96	
Rev	ECN No.	Date	
B	97-139	3-26-97	

SPECIAL INSTRUCTIONS