
REV:
 DCR #
 DATE:

 B
 D060243
 Feb 6, 2018

REV PER ECO 17-018324



## KIT DESCRIPTION

ITEM	DESCRIPTION	MATERIAL
1	BODY ASSEMBLY – 45° SWEPT	ALUMINIUM ALLOY
2	CLAMPING NUT - PLAIN	ALUMINIUM ALLOY
3	CONIC RING	ALUMINIUM ALLOY
4	STAR	ALUMINIUM ALLOY

© 2006 Tyco Electronics Corporation. All rights reserved.

<b>tyco</b> / <i>Electronics</i> Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	TITLE: HEXASHIELD S FOR CODE 40 PLAIN CL/	CONNEC	CTORS-
ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN REACKETS confidence. Publication		information set forth hereon is the ronics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by ohibited.	DOCUMENT NO. HEX40-AY-45	S-YY-AY	′Y-1-YY	
DRAWN: IRT	DATE: SEP 00		rves the right to amend this drawing ould evaluate the suitability of the cation.	FILE: D060243	SCALE: NONE	SHEET: 1 OF 4


 REV:
 DCR #
 DA

 B
 D060243
 Feb 6

## TABLE OF DIMENSIONS

Order Number	Shell Size		ØA Thread Class 6H	<b>ØВ</b> Мах	<b>ØC</b> Max	D Max	E Max	-	rule ntity
	Mil.	Com.						Std.	Opt.
09	A	09	M12 x 1	19.0 [0.75"]	17.5 [.689]	14.0 [0.55"]	26.0 [1.02"]	1	-
11	В	11	M15 x 1	22.0 [0.87"]	21.5 [.846]	14.0 [0.55"]	26.0 [1.02"]	2	-
13	С	13	M18 x 1	25.5 [1.00"]	22.5 [.886]	14.0 [0.55"]	26.0 [1.02"]	3	-
15	D	15	M22 x 1	30.5 [1.20"]	28.5 [1.122]	16.0 [0.63"]	28.0 [1.10"]	5	-
17	E	17	M25 x 1	33.5 [1.32"]	31.5 [1.240]	16.0 [0.63"]	28.0 [1.10"]	6	7
19	F	19	M28 x 1	37.0 [1.46"]	35.0 [1.378]	16.0 [0.63"]	28.0 [1.10"]	7	-
21	G	21	M31 x 1	38.5 [1.52"]	38.0 [1.496]	18.0 [0.71"]	30.0 [1.18"]	9	11
23	Н	23	M34 x 1	42.0 [1.65"]	41.0 [1.614]	18.0 [0.71"]	30.0 [1.18"]	10	13
25	J	25	M37 x 1	46.5 [1.83"]	46.0 [1.811]	18.0 [0.71"]	30.0 [1.18"]	12	17

### PART NUMBERING



### **APPLICATION**

- These adaptors are designed to be mounted on the following connectors:


MIL-C-38999 Series III and IV

<b>tyco</b> / <i>Electronics</i> Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	HEXASHIELD S FOR CODE 40 PLAIN CLA	CONNEG	CTORS-
ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS confidence. Publicat			information set forth hereon is the ronics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by ohibited.	DOCUMENT NO. HEX40-AY-45	S-YY-AY	′Y-1-YY
DRAWN: IRT	DATE: SEP 00		rves the right to amend this drawing ould evaluate the suitability of the cation.	FILE: D060243	SCALE: NONE	SHEET: 2 OF 4

 REV:
 DCR #
 DATE:

 B
 D060243
 Feb 6, 2018

- They are qualified to the Raychem specification RB-114, when installed on metallic Mil-Specification circular connectors only.
- They are designed primarily for open wire bundle installation but are also designed to accept Raychem heat shrink moulded parts where strain relief is required see illustration on sheet 3.



- Use in conjunction with the ferrules HET-A-0XX, which are purchased separately. Refer to HET-A-0XX S.C.D. for relevant selection details.

### **INSTALLATION**

- See Installation Procedure RPIP-696-04.


### PACKAGING

- All components are supplied in a plastic bag.

### NOTES!

1. Item 4 - Star - is not supplied with Hexashield Order Number 09.

2. The DS option, illustrated below, is for a Drilled Star that is available on sizes 15 to 25 only. This option is to allow unshielded wires to pass through the assembly.



				-	-	
STAR SIZE	15	17	19	21	23	25
ØD MAX	3.0	6.0	9.0	12.0	15.0	18.0
	[0.12"]	[0.24"]	[0.35"]	[0.47"]	[0.59"]	[0.71"]

<b>tyco</b> / <i>Electronics</i> Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	TITLE: HEXASHIELD S FOR CODE 40 PLAIN CLA	CONNEC	CTORS-
ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS confidence. Publicati		nformation set forth hereon is the ronics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by shibited.	DOCUMENT NO. HEX40-AY-45	S-YY-AY	Y-1-YY	
DRAWN: IRT	DATE: SEP 00		rves the right to amend this drawing ould evaluate the suitability of the ation.	FILE: D060243	SCALE: NONE	SHEET: 3 OF 4


 REV:
 DCR #
 DATE:

 B
 D060243
 Feb 6, 2018

3. Where the ferrule quantities required are standard, the item 4 - Star - is also standard. If the optional quantity is selected then 2 items 4 will be supplied - one "split" and the other one standard. See below for illustration.

EXAMPLE: FERRULE QUANTITY CODE -A13

-A13 = -A10 SPLIT STAR + -A3 STANDARD STAR



4. Assembly is to be permanently marked with Code Identity Number and Part Number. (e.g. 06090 HEX40-AB-45S-21-A9-1)

<b>THED</b> / Electronics Wire and Harnessing Products			Raychem Wire and Harnessing Products 300 Constitution Drive Menlo Park, CA 94025 USA	TITLE: HEXASHIELD S FOR CODE 40 PLAIN CLA	CONNEC	CTORS-
ARE IN MILLIMETERS. INCH DIMENSIONS ARE SHOWN IN BRACKETS			information set forth hereon is the ronics and is to be held in trust and n, duplication, disclosure or use for expressly authorized in writing by ohibited.	DOCUMENT NO. HEX40-AY-45	S-YY-AY	′Y-1-YY
DRAWN: IRT	DATE: SEP 00		rves the right to amend this drawing ould evaluate the suitability of the cation.	FILE: D060243	SCALE: NONE	SHEET: 4 OF 4