



P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	INITIAL RELEASE	11FEB2021	MN	AK

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: C44179-000

OUTSIDE WOUND LABEL ACROSS: 1 PER ROLL QTY: 1300

MATERIAL	HIGH TACK MATTE METALIZED POLYESTER				
ADHESIVE TYPE	PERMANENT				
LINER	GLASSINE PAPER				
DWN	M. NUTTALL	11FEB2021	TE Connectivity		
CHK	A. KEAN	12FEB2021			
APVD	A. KEAN	12FEB2021			
PRODUCT SPEC	TTDS-118				
APPLICATION SPEC	-		NAME		
HMM - HIGH TACK MATTE METALIZED POLYESTER			-		
WEIGHT	1.344g	A3	C2290	C-HMM-101101-1.3-8A	RESTRICTED TO
CUSTOMER DRAWING			SCALE	NTS	SHEET
			1 OF 1	REV	C

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL	FINISH
SEE TABLE	-