



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT - TE Connectivity Ltd. ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE AND MATERIAL RE-DESIGN	25APR2019	GK	KM

**LABEL AND LINER DESIGN**



**PRESENTATION**



All dimensions in mm [Inches]

**TE PN: 483818-000**

**OUTSIDE WOUND  
 LABEL ACROSS: 1  
 PER ROLL QTY: 5000.  
 ROLL LENGTH: 40.5m**

<b>MATERIAL</b>	WHITE POLYPROPYLENE FILM
<b>ADHESIVE TYPE</b>	PERMANENT
<b>LINER</b>	BLEACHED, SUPER-CALENDERED PAPER STOCK

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES ± -	
MATERIAL SEE TABLE	FINISH -

DWN K. RAGHAVENDRA 23MAY2016		TE Connectivity		
CHK K. MUNZ 23MAY2016		NAME HPK - THERMAL TRANSFER PRINTABLE PANEL LABELS		
APVD K. MUNZ 23MAY2016		PRODUCT SPEC TTDS-008		
APPLICATION SPEC	SIZE A3	CAGE CODE C2290	DRAWING NO HPK02WE1050	RESTRICTED TO
WEIGHT 0.082 g	CUSTOMER DRAWING			SCALE NTS
SHEET 1 of 1			REV B	

HPK02WE1050