

# CUSTOMER PROOFING/CONFORMANCE FORM



**Tyco Electronics**

Our commitment. Your advantage

Tyco Electronics Idento GmbH

Paul-Ehrlich-Str. 23  
63322 Rödermark

Telephone: +49(0) 6074 8908 (0)  
Facsimile: +49(0) 6074 8908 82  
E-mail: [idento@tycoelectronics.com](mailto:idento@tycoelectronics.com)  
Website: [www.idento.de](http://www.idento.de)

Attention of: *Tyco Electronics*

Drawing No.: *KMT-07323V-9*

Tyco Part: *5-1768021-8*

Name: \_\_\_\_\_ Signature: \_\_\_\_\_

Date: \_\_\_\_\_



## PLEASE NOTE

**This form is an important part of our contract review and your order cannot be processed further until the necessary approval has been obtained.**




We wish to provide a quality service to you and are conscious that a lengthy delay at this stage could affect any quoted delivery requirements. Delays in excess of 2 working days could result in delivery times being untenable. Please indicate below your acceptance and/or amendments and return this form as soon as is practicable.

**Any amendments to the original design will be charged out @ Euros 40 each conformance to cover administration**

**Orders which remain on conformance with a customer for more than 2 weeks are placed in quarantine this may result in no further action or possible cancellation, however please be assured that we will attempt to contact you before this action**


## LABEL SPECIFICATION

These are our standard tolerances unless specified by customers drawing



## FONTS

Label build detail




All dimensions in mm

|                   |                                   |
|-------------------|-----------------------------------|
| Material          | <i>PV406 soft PVC</i>             |
| Adhesive Type     | <i>Permanent acrylic adhesive</i> |
| Nom. Thickness    | <i>0,08mm</i>                     |
| Overlaminated Y/N | <i>no</i>                         |
| Texture           | <i>gloss</i>                      |
| Print Colours     | <i>white</i>                      |
| Background Colour | <i>transparent</i>                |
| Wound             | <i>Inside Wound</i>               |

|                                            |                         |                                                 |                                            |
|--------------------------------------------|-------------------------|-------------------------------------------------|--------------------------------------------|
| <b>TITLE</b><br><i>KMT-07323</i>           | <b>REV</b><br><i>A1</i> | <b>DRAWN BY</b><br><i>IP</i><br><i>29/06/10</i> | <b>DRAWING No.</b><br><i>KMT-07323V-9</i>  |
| <b>MODIFICATION</b>                        |                         | <b>DATE</b>                                     | <b>PLAN No.</b><br><i>SAP: 5-1768021-8</i> |
| <b>APPROVED BY</b><br><i>N. Harputoglu</i> |                         | <b>DATE</b>                                     | <b>FOLDER</b><br><i>Rödermark Juni10</i>   |
|                                            |                         |                                                 | <b>PAGE 1</b><br><i>Customer</i>           |

## PRESENTATION

All dimensions in mm



## PRINTING / DIMENSION

max. outside cable Ø = 15,0mm

