


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - LEB-0608P-4 ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	DRAWING FORMAT UPDATE	21DEC2018	GK	KM



LABEL ACROSS: 11
LABELS PER SHEET: 330
LABELS PER PACK: 3300
SHEETS PER PACK: 10

All dimensions in mm [INCHES]

Print Colour	Description	Material	Nom. Thickness	Adhesive Type	Part number
	LEB-0916P-8A	PE200 Silver Polyester	0.05 mm	Acrylic, permanent	5-1768033-7
	LEB-0916P-9	PE201 White Polyester	0.05 mm	Acrylic, permanent	5-1768033-8
	LEB-0916P-8	PE202 Silver-grey Polyester	0.05 mm	Acrylic, permanent	5-1768033-6
	LEB-0916P-4	PE216 Yellow Polyester	0.05 mm	Acrylic, permanent	5-1768033-5
	LEB-0916PF-4	GW201 Yellow Polyester cloth	0.10 mm	Acrylic, permanent	5-1768033-9

TOLERANCES mm [INCHES]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±

MATERIAL: SEE TABLE

FINISH: -

DWN	21DEC2018		TE Connectivity	
CHK	21DEC2018		LEB - POLYESTER LABELS ON SHEET	
APVD	21DEC2018	NAME	-	
PRODUCT SPEC		APPLICATION SPEC	-	
WEIGHT	0.05 g	SIZE	A2	RESTRICTED TO
CUSTOMER DRAWING		CAGE CODE	C2290	
		DRAWING NO	LEB-0916	
		SCALE	NTS	
		SHEET	1 of 1	
		REV	B	