


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	2	DRAWING UPDATE	10AUG2022	GSK	SR



	Maximum system voltage [kV]	Cable cross section [mm ²]	Application Type	Bushing types	Bushing length [mm]
RSRB-4022	17.5	10 - 35	Inline connection	DIN, CENELEC, ANSI	n/a
RSRB-4024	17.5	50 - 95	Inline connection	DIN, CENELEC, ANSI	n/a
RSRB-4026	17.5	120 - 300	Inline connection	DIN, CENELEC, ANSI	n/a
RSRB-4042	17.5	10 - 35	Elbow connection	DIN, CENELEC, ANSI	90 - 130
RSRB-4044	17.5	50 - 95	Elbow connection	DIN, CENELEC, ANSI	90 - 130
RSRB-4046	17.5	120 - 300	Elbow connection	DIN, CENELEC, ANSI	90 - 130
RSRB-4062	17.5	10 - 35	Elbow connection	DIN, CENELEC, ANSI	60 - 90
RSRB-4064	17.5	50 - 95	Elbow connection	DIN, CENELEC, ANSI	60 - 90
RSRB-4066	17.5	120 - 300	Elbow connection	DIN, CENELEC, ANSI	60 - 90

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SATHISH KUMAR G 17MAR2021	 TE Connectivity				
DIMENSIONS: mm		CHK ANGEL M. 17MAR2021				NAME RSRB	
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD JORDI VALENCIA 17MAR2021	PRODUCT SPEC -				
MATERIAL -		FINISH -	APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO G-MV_CA_SWG_RSRB	RESTRICTED TO -
CUSTOMER DRAWING			WEIGHT	SCALE NTS	SHEET 1 OF 1	REV 2	