



P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-21-110870	26AUG2021	GK	MN

LABEL AND LINER DESIGN



PRESENTATION



All dimensions in mm [Inches]

TE PN: C32547-000

**OUTSIDE WOUND
LABEL ACROSS: 4
PER ROLL QTY: 10000**

MATERIAL	NYLON CLOTH
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL SEE TABLE	FINISH -

DWN GOPALAKRISHNA HV 26AUG2021	TE Connectivity			
CHK MIKE NUTTALL 26AUG2021				
APVD MIKE NUTTALL 26AUG2021	NAME NC - NYLON CLOTH LABELS			
PRODUCT SPEC TTDS-051	SIZE A3	CAGE CODE C2290	DRAWING NO G-NC-191064-10-9	RESTRICTED TO -
APPLICATION SPEC -	WEIGHT 0.039g	SCALE NTS	SHEET 1 OF 1	REV B
CUSTOMER DRAWING				