



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	INITIAL RELEASE	27AUG2021	GK	MN

### LABEL AND LINER DESIGN



### PRESENTATION



All dimensions in mm [Inches]

**TE PN: A63636-000**

**OUTSIDE WOUND  
LABEL ACROSS:3  
PER ROLL QTY: 10000**

MATERIAL	NYLON CLOTH
ADHESIVE TYPE	PERMANENT ACRYLIC
LINER	GLASSINE PAPER

TOLERANCES mm [INCH]	
LABEL HEIGHT:	±0.3 [.012]
LABEL WIDTH:	±0.3 [.012]
WEB WIDTH:	±0.8 [.031]
VERTICAL REPEAT:	±0.8 [.031]*
HORIZONTAL REPEAT:	±0.8 [.031]*
PRINT POSITIONING:	±0.8 [.031]*
LEFT MARGIN:	±0.4 [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL SEE TABLE	FINISH -

DWN	27AUG2021
CHK	GOPALAKRISHNA HV
APVD	27AUG2021
NAME	MIKE NUTTALL
PRODUCT SPEC	TTDS-051
APPLICATION SPEC	-
WEIGHT	0.046g

TE Connectivity			
NAME NC - NYLON CLOTH LABELS			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	C2290	NC-254064-10-9	-
CUSTOMER DRAWING		SCALE	SHEET
		NTS	1 OF 1
		REV	F