


SHELL SIZE	A THREAD	B MAX	C MAX	D MAX	E MAX	F MAX	G	H MAX
08	1/16 -28UNEF	18,3	16,6	20,6	22,7	26,5	6,8	13,5
10	9/16 -24UNEF	21,5	17,4	21,4	26,2	28,2	10,2	15,4
12	1 1/16 -24UNEF	24,5	17,8	22,3	29,2	29,7	13,1	19,7
14	3/16 -20UNEF	27,8	18,7	22,7	32,2	31,2	16,3	21,3
16	5/16 -20UNEF	30,8	20,4	23,5	35,7	32,9	19,5	24,5
18	1 1/16 -18UNEF	34,1	19,8	23,8	39,7	34,5	21,9	26,5
20	1 3/16 -18UNEF	37,3	20,6	24,6	42,2	36,2	25,0	31,0
22	1 5/16 -18UNEF	40,5	21,0	25,5	45,2	37,7	28,4	34,4
24	1 7/16 -18UNEF	43,7	21,9	25,9	48,2	39,2	31,5	36,6

97M1-16-1-C

SERIES
CONNECTOR INTERFACE
ANGLE
SHELL SIZE
MATERIAL
PLATING

SPIN COUPLING ADAPTOR	SERIES 97 TO FIT CONNECTOR CODE M
THIS DRAWING IS THE COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT WRITTEN CONSENT OF THE COMPANY	
 POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	