

REV	DESCRIPTION	DRAWN	DATE
BC	ECR-23-183226	N.H	21/08/23
BD	ECR-24-204762	N.H	03/04/24




TABLE 2

PCR SIZE CODE	B
8,1	8,1
9,1	9,1
10,0	10,0
11,9	11,9
12,6	12,6
15,1	15,1
16,1	16,1
18,0	18,0
19,4	19,4
21,4	21,4
22,6	22,6
23,0	23,0
24,6	24,6
25,8	25,8
27,8	27,8
28,8	28,8
30,6	30,6
32,0	32,0
34,1	34,1
35,0	35,0
36,9	36,9
37,7	37,7
38,3	38,3
40,1	40,1
41,7	41,7
42,8	42,8
44,6	44,6
57,5	57,5









TABLE 1

EYELET SIZE CODE	A
00	NA (FREE END)
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

STANDARD EYELET MATERIAL IS TINNED COPPER, EXCEPT IN LINK CHAIN ASSEMBLIES WHICH ARE STAINLESS STEEL THROUGHOUT

TABLE 3

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE E DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD POLYPROPYLEEN
VGB	1,5MM BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD
LWB	NYLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE (1,0MM DIAMETER)
LWBF	FEP COVERED STAINLESS STEEL WIRE ROPE (1,0MM DIAMETER)

LIST NOT EXHAUSTIVE - FOR COMPREHENSIVE LIST AND SPECS SEE WEBSITE

ALTERNATIVE PART NUMBER BREAKDOWN  
FOR LANYARD LENGTH IN INCHES

LAN-E03-WR6-E03

LENGTH IN INCHES  
'Lxxx' IS OMITTED WHEN LENGTH OF LANYARD IS REQUIRED IN INCHES

NOTE

LANYARD OR LINK CHAIN LENGTH IS MEASURED FROM THE CENTER OF EYELETS ON EITHER END.

IF ONLY ONE EYELET IS PRESENT IN THE ASSEMBLY, MEASURE FROM THE CENTER OF EYELET TO THE END OF THE LANYARD.

EXTRA ATTACHMENTS ARE NOT INCLUDED IN THE LANYARD LENGTH MEASUREMENT.

SERIES \_\_\_\_\_




END A \_\_\_\_\_

(E\*\* - EYELET (\*\* - SIZE CODE SEE TABLE 1))  
(PCA-LCE EYELET (FOR LINK CHAIN CAP ATTACHMENT END ONLY))  
(PCR\*\*\* - PCR RING (\*\*. \* - SIZE CODE SEE TABLE 2))  
(CF - CRIMP FERRULE)  
(SR - SPLIT RING)  
(TR - TIE WRAP)  
LANYARD TYPE (SEE TABLE 3) \_\_\_\_\_

LENGTH IN MM \_\_\_\_\_

END B \_\_\_\_\_

(E\*\* - EYELET (\*\* - SIZE CODE SEE TABLE 1))  
(PCR\*\*\* - PCR RING (\*\*. \* - SIZE CODE SEE TABLE 2))  
(CF - CRIMP FERRULE)  
(SR - SPLIT RING)  
(SPCR\*\*\* - SPLIT PCR RING (\*\*. \* - SIZE CODE SEE TABLE 2)  
(TR - TIE WRAP)

DRAWN		DATE			PART NUMBER:					
C.WALLACE		09/10/2012			LAN SERIES					
APPROVED BY										
M.PAUL		08/10/2018		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES <b>GENERAL TOL</b> LINEAR +/-0,25MM ANGULAR +/- 1°	TITLE:  GENERAL LANYARD KIT					
CHECKED BY										
R.STYLES		08/10/2018		<b>MATERIAL</b>  SEE PART NUMBER BREAKDOWN  <b>FINISH</b>  SEE PART NUMBER BREAKDOWN	ASSY USED ON:			RESTRICTED TO:		DRAWING NO: <b>P11078</b>
<div>DOC TYPE</div> Customer Drawing										
<div>ISSUE/REV</div> <b>BD</b>		<div>DCR</div> ---								
NCAGE CODE U5792		<div>WEIGHT</div> N/A								
					THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		