



TABLE 1

CLASS	MATERIAL/FINISH
F	ALUMINIUM/NICKEL PLATED
K	STAINLESS STEEL/PASSIVATED
W	ALUMINIUM/OLIVE DRAB CADMIUM PLATED
Z	ALUMINIUM/ZINK NICKEL PLATED

TABLE 2

SHELL SIZE	A MAX	B MAX	C THREAD	D MIN	E MAX	G MAX	H MAX	J MAX	I MIN	N	MAXIMUM ENTRY SIZE
09	21,79	15,24	M12x1,0-6H	6,70	16,76	14,85	10,20	31,05	2,90	12	D
11	24,99	18,21	M15x1,0-6H	9,90	16,76	16,60	13,70	34,21	2,90	16	F
13	29,39	21,18	M18x1,0-6H	12,80	16,76	18,15	16,80	37,95	2,90	20	H
15	32,49	25,14	M22x1,0-6H	16,00	16,76	19,50	17,90	39,65	2,90	24	J
17	35,71	28,12	M25x1,0-6H	19,20	16,76	21,10	21,20	41,25	2,90	28	K
19	38,50	31,09	M28x1,0-6H	21,40	16,76	22,10	23,20	43,75	2,90	32	K
21	41,70	34,04	M31x1,0-6H	24,60	16,76	23,60	26,20	46,91	2,90	36	L
23	44,91	36,90	M34x1,0-6H	27,70	16,76	25,20	29,40	50,10	2,90	40	M
25	47,98	39,88	M37x1,0-6H	30,90	16,76	26,90	32,60	53,26	1,70	44	M

TABLE 4

CABLE ENTRY SIZE CODE	AA +/-0,1	BB +/-0,1	CC +/-0,3	DD +0,2/-0
A	4,7	7,7	12,2	1,12
B	6,4	9,4	14,0	1,12
C	7,9	11,0	15,5	1,12
D	9,5	12,6	17,1	1,12
E	11,1	14,1	18,7	1,12
F	12,7	15,7	20,3	1,12
G	15,9	18,9	23,5	1,12
H	19,1	22,0	26,7	1,12
J	22,2	25,2	29,8	1,75
K	25,5	28,4	33,0	1,75
L	28,6	31,5	36,2	1,75
M	31,8	34,7	39,4	1,75

\* NOTES:

- 1 - MINIMUM PENETRATION OF ØD FROM FRONT OF SERRATIONS
- 2 - PLEASE NOTE THERE MAY BE CROSSOVER DEPENDENT ON DIAMETER AND PITCH

EN3660-062W15B

SERIES

CLASS, MATERIAL FINISH (TABLE 1)

SHELL SIZE (TABLE 2)

CABLE ENTRY SIZE CODE (TABLE 4)

DRAWN	W.RUST	DATE	26/04/2018
SALES APPR	H.TAILLANDIER	DATE	26/04/2018
DESIGN APPR	M.PAUL	DATE	17/12/2014
PROD APPR	J.STEPHENSON	DATE	17/12/2014
QUAL APPR	P.REES	DATE	17/12/2014
ISSUE	DCR		
3	6780		
NCAGE CODE	U5792	WEIGHT	

3RD ANGLE PROJECTION NOT TO SCALE
UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
GENERAL TOL LINEAR +/-0,25MM ANGULAR +/- 3°
MATERIAL SEE ABOVE
FINISH SEE ABOVE



**POLAMCO LTD**  
www.polamco.com

WESTON LOCK  
LOWER BRISTOL ROAD  
BATH BA2 1EP

ASSY USED ON: MIL-DTL-38999 SERIES III & IV

TITLE:  
**90° ANTI-DECOUPLING BANDING ADAPTOR**

PART NUMBER:  
**EN3660-062\*\*\*\*\***

THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD  
IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.

DRAWING NO: SHT  
**P18068 1**