



WITH ATTACHMENT



ATTACHMENT OPTIONS:



OMIT FOR NO ATTACHMENT
(SEE SHEET 2)

P83723/60-2-14-1-C-WR4-03

SERIES —
60 - RECEPTACLE —
2 - BAYONET COUPLING —
INSERT F FOR —
FLUROSILICONE GASKET —
OMIT FOR STANDARD —
SILICONE GASKET —
SHELL SIZE (TABLE 1) —
MATERIAL (TABLE 5) —
FINISH (TABLE 6) —
LANYARD TYPE (TABLE 4) —
LANYARD LENGTH (IN INCHES) —
+1,0"/-0" TOLERANCE —
ATTACHMENT (SEE ABOVE) —

DRAWN	W.RUST	DATE 13/10/2011	 3RD ANGLE PROJECTION NOT TO SCALE	 POLAMCO LTD	WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 1	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR	J.L.MODJTBAI	13/10/2011					
DESIGN APPR			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: MIL-DTL-83723 SERIES (BAYONET)			MATERIAL SEE ABOVE
QUAL APPR				TITLE: RECEPTACLE PROTECTION COVER			
ISSUE 2	DCR 3969			PART NUMBER: P83723/60-2 SERIES			NCAGE CODE U5792
WEIGHT ---		GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°					DRAWING NO: P20132

TABLE 1

SHELL SIZE	ØA MAX	ØB MIN	ØC MIN
08	19,71	16,05	13,72
10	23,01	19,71	16,81
12	27,38	23,62	21,13
14	28,98	25,37	22,89
16	32,16	28,60	26,11
18	34,93	31,29	28,80
20	38,35	34,47	32,03
22	41,28	37,64	35,15
24	44,70	40,82	38,38

TABLE 2

EYELET REF.	ØF
01	3,2
02	3,7
03	4,3
04	5,3
05	6,4

TABLE 3

RING REF.	ØE
08	15,1
10	18,0
12	22,6
14	25,8
16	28,8
18	32,0
20	35,0
22	38,3
24	41,7

TABLE 4

CODE	LANYARD TYPE
WR	NYLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
TC	TEFLON COVERED (CLEAR) STAINLESS STEEL WIRE ROPE
WG	TEFLON COVERED (OLIVE DRAB) STAINLESS STEEL WIRE ROPE
WB	TEFLON COVERED (BLACK) STAINLESS STEEL WIRE ROPE
WRB	PVC COVERED (BLACK) STAINLESS STEEL WIRE ROPE
LC	LINK CHAIN
BK	BLACK CORD
VGB	1,5mm BLACK POLYESTER CORD EQV. TO DIN83330-E1,5
B	BEAD CHAIN
R	OLIVE DRAB POLYESTER CORD
NB	OLIVE DRAB NYLON CORD
NK	BLACK NYLON CORD

TABLE 5

CODE	MATERIAL
1	ALUMINIUM
2	NICKEL ALUMINIUM BRONZE
4	STAINLESS STEEL


LIST NOT EXHAUSTIVE, SEE MATERIAL TABLE
FOR OTHER OPTIONS

TABLE 6


CODE	DESCRIPTION
B	CADMIUM, OLIVE DRAB OVER ELECTROLESS NICKEL
C	ELECTROLESS NICKEL
G	BLACK ANODISE, SULPHURIC
J	PASSIVATE
U	UNPLATED CLEAN FINISH NOT SHOT BLASTED
Z	SHOT BLAST FOR NON-REFLECTIVE FINISH
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

LIST NOT EXHAUSTIVE, SEE PLATING TABLE FOR OTHER OPTIONS

WITHOUT ATTACHMENT



P83723/60-2-14-1-C
NO ATTACHMENT VERSION
SIMILAR TO M83723/60-2**AN



P83723/60-2-14-1-C-EO
EYELET ONLY VERSION
(NO LANYARD)

DRAWN	W.RUST	DATE 13/10/2011	 3RD ANGLE PROJECTION NOT TO SCALE	 POLAMCO LTD WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	PAGE 2	UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES
SALES APPR	J-L.MODJTBAI	13/10/2011				
DESIGN APPR						
QUAL APPR						
ISSUE 2	DCR 3969		THIS DRAWING IS COPYRIGHTANDTHE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.	ASSY USED ON: MIL-DTL-83723 SERIES (BAYONET)		MATERIAL SEE ABOVE
WEIGHT ---				TITLE: RECEPTACLE PROTECTION COVER		
				PART NUMBER: P83723/60-2 SERIES		DRAWING NO: P20132
GENERAL TOL LINEAR +/-0.1MM ANGULAR +/- 1°						