





T OPTION
PROVIDES CUTOUTS IN ORDER TO
ACCOMMODATE TABS




HARDWARE OPTIONS


CODE: SSL
SHORT
SLOTTED
HEAD SCREW




CODE: H
HEX SOCKET
HEAD SCREW




CODE: F
JACK POST
(4-40 UNC)




CODE: 0
NO HARDWARE
SUPPLIED



CODE: PF-0
THREADED
HOLE
4-40 UNC



CODE: M3-0
THREADED
HOLE
M3



4-40UNC - 2B
NOT
SUPPLIED
WITH
HARDWARE

M3x0.5 - 6H
NOT
SUPPLIED
WITH
HARDWARE

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: D**-3-SB-**-**-L**-**-** D**-3D-SB-**-**-L**-**-**			 Polamco		
B.VESA		09/02/2018								
DESIGN APPROVAL		DATE		TITLE: REVERSIBLE 90DEG D-SUB BANDING BACKSHELL						
K.SHEPPARD		05/04/2018		UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/-0.25MM ANGULAR +/- 1°			ASSY USED ON: MIL-DTL-24308		 TE connectivity	
DOC TYPE	Customer Drawing			MATERIAL						
ISSUE AA	REV.	DCR 6701		SEE PART NUMBER BREAKDOWN						
NCAGE CODE U5792		WEIGHT 13.23 g		FINISH		THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.		POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP	SHT 1	DRAWING NO P22008
				SEE PART NUMBER BREAKDOWN						

D25-3*-SB-07-1-C-T-L20-E-SB

CONNECTOR TYPE
SHELL SIZE (TABLE 1)
ENTRY POSITION
SIDE ENTRY, REVERSIBLE
TERMINATION STYLE
SB - BAND TERMINATION STYLE
ENTRY SIZE (TABLE 2)
MATERIAL (TABLE 3)
PLATING (TABLE 3)
T OPTION
OMIT FOR STANDARD FLANGE
OPTIONAL LENGTH (5MM INCREMENTS)
SEE TABLE 2 FOR MIN
(IF OMITTED, L30 WILL BE SUPPLIED)
HARDWARE OPTION
OMIT FOR STANDARD
BAND REFERENCE
SB = STANDARD BAND
OMIT IF NO BAND REQUIRED

* - ENTRY POSITION 3D ALSO ACCEPTABLE

TABLE 1

SHELL SIZE	MIL SPEC SHELL SIZE REFERENCE	A	B	C	D	MAX ENTRY
09	1	31,19	25,00	12,93	22,86	07
15	2	39,52	33,33	12,93	31,09	07
25	3	53,42	47,02	12,93	44,86	07
37	4	69,76	63,50	12,93	61,32	07
50	5	67,31	61,12	15,75	58,98	08
104	6	69,70	63,50	17,35	NA	09

TABLE 2

ENTRY SIZE (CIRCULAR)	ØG	ØH MAX	L MIN
01	3,18	6,78	20
02	4,75	8,35	25
03	6,86	10,46	25
04	7,37	10,97	25
05	7,92	11,52	25
06	10,03	13,63	30
07	10,67	14,27	30
08	12,70	16,30	30
09	14,27	17,90	30

TABLE 3

CODE	MATERIAL / PLATING
1-C	ALUMINIUM / ELECTROLESS NICKEL
1-B	ALUMINIUM / CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
1-ZN	ALUMINIUM / ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL
1-Y	ALUMINIUM / YELLOW CHROMATE OVER CADMIUM
4-J	STAINLESS STEEL / PASSIVATE

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER: D**-3-SB-**-**-L**-**-**		 Polamco
B.VESA		09/02/2018			D**-3D-SB-**-**-L**-**-**		
DESIGN APPROVAL		DATE		TITLE: REVERSIBLE 90DEG D-SUB BANDING BACKSHELL		 TE	
K.SHEPPARD		05/04/2018		ASSY USED ON: MIL-DTL-24308			
DOC TYPE	Customer Drawing			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			
ISSUE	REV.	DCR	MATERIAL		POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP		DRAWING NO: P22008
AA		6701	SEE PART NUMBER BREAKDOWN		SHT 2		
NCAGE CODE U5792		WEIGHT	FINISH				
		13.23 g	SEE PART NUMBER BREAKDOWN				