


SHELL SIZE	A THREAD	ØB MAX	ØG	ØH MAX	C MAX	D MAX	E MAX	F MAX	K ± 0,5
09	M12 x 1.0	18,0	6,8	13,2	12,5	14,5	20,0	21,5	13,5
11	M15 x 1.0	21,0	10,3	16,7	13,0	15,0	23,0	23,0	14,5
13	M18 x 1.0	24,5	13,6	20,0	13,6	15,5	27,0	24,5	17,0
15	M22 x 1.0	29,0	16,3	22,7	14,0	16,0	28,0	28,5	16,5
17	M25 x 1.0	32,5	19,5	25,4	15,0	17,0	31,0	30,0	18,0
19	M28 x 1.0	35,5	21,9	28,3	16,0	18,0	36,0	31,5	21,0
21	M31 x 1.0	37,0	25,2	31,6	16,6	18,5	39,0	33,0	22,0
23	M34 x 1.0	40,0	28,3	34,7	17,0	19,0	41,0	34,5	23,0
25	M37 x 1.0	43,5	31,5	37,9	17,4	19,5	47,0	36,0	27,5

DOUBLE SLOT OPTION	L ±0,5	M ±0,2	N ±0,2	MESH-TAPE PART NUMBER (ORDERED SEPARATELY - 25 M REEL)
D1	26,5	12,0	19,5	KM (6)
D2	34,5	20,0	27,5	KM (13)


CODE	FINISH
C	ELECTROLESS NICKEL
B	CADMIUM OLIVE DRAB OVER ELECTROLESS NICKEL
ZB	ZINC COBALT OLIVE DRAB OVER ELECTROLESS NICKEL
ZN	ZINC NICKEL BLACK PASSIVATE OVER ELECTROLESS NICKEL

SEE SS0076 FOR FULL RANGE OF FINISH OPTIONS



KMAH1-17-1-C-D1-HE

SERIES _____
STYLE _____
CONNECTOR INTERFACE _____
ANGLE _____
SHELL SIZE (TABLE 1) _____
MATERIAL _____
ALUMINIUM ALLOY _____
FINISH (TABLE 3) _____
DOUBLE SLOT OPTION (TABLE 2) _____
TERMINATION OPTION _____
HE - CONSTANT FORCE SPRING
OMIT FOR SUPPLIED WITHOUT SPRING

DRAWN		DATE		 3RD ANGLE PROJECTION NOT TO SCALE	PART NUMBER:					 Polamco  TE connectivity	
K.WINCZURA		20/03/2013			KMAH-D SERIES						
DESIGN APPROVAL		DATE			TITLE:						
K.SHEPPARD		04/04/2013									
				UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS IN MILLIMETRES GENERAL TOL LINEAR +/- 0,25MM ANGULAR +/- 1°	MESH TAPE BACKSHELL, DOUBLE SLOT						
DOC TYPE		Customer Drawing		MATERIAL SEE PART NUMBER BREAKDOWN FINISH SEE PART NUMBER BREAKDOWN	ASSY USED ON: MIL-DTL-38999 SERIES III & IV			RESTRICTED TO:			SHT 2
ISSUE/REV AA		DCR ---			THIS DRAWING IS COPYRIGHT AND THE PROPERTY OF POLAMCO LTD IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF THE COMPANY.			POLAMCO LTD, WESTON LOCK, LOWER BRISTOL ROAD BATH BA2 1EP			
NCAGE CODE U5792		WEIGHT N/A									
											DRAWING NO: P25784