







SHELL SIZE	A THREAD CLASS 2B	B MAX	C MAX	D MAX	E MAX	F MAX
08	$7/16$ -28UNEF	17.3	14.5	17.5	25.5	24.5
10	$9/16$ -24UNEF	20.3	15.5	18.5	28.5	26.0
12	$11/16$ -24UNEF	23.8	16.0	19.0	32.0	27.5
14	$13/16$ -20UNEF	26.8	16.5	19.5	35.5	29.0
16	$15/16$ -20UNEF	29.8	17.0	20.5	38.5	30.5
18	$1 1/16$ -18UNEF	33.3	17.5	21.0	42.0	32.5
20	$1 3/16$ -18UNEF	36.3	18.5	21.5	45.5	34.0
22	$1 5/16$ -18UNEF	39.3	19.0	22.0	48.5	35.5
24	$1 7/16$ -18UNEF	42.8	20.0	23.0	51.5	37.0

ENTRY SIZE	G MAX	H MAX
03	4.77	11.4
04	6.35	12.9
05	7.92	14.5
06	9.52	16.0
07	11.10	17.6
08	12.70	19.2
09	14.27	20.8
10	15.88	22.4
11	17.47	24.0
12	19.05	25.6
13	20.62	27.2
14	22.23	28.8
15	23.82	30.4
16	25.40	31.9
17	27.00	33.5
18	28.60	35.1
19	30.20	36.7
20	31.80	38.2

SERIES _____
 CONNECTOR INTERFACE _____
 ANGLE _____
 SHELL SIZE _____
 ENTRY SIZE _____
 MATERIAL _____
 PLATING _____

97K3-16-08-1-C

SPIN COUPLING ADAPTOR	SERIES 97 (P3557) TO FIT CONNECTOR CODE K
	THIS DRAWING IS THE COPYRIGHT AND THE PROPERTY OF POLAMCO LTD. IT MUST NOT BE COPIED, USED FOR MANUFACTURE OR OTHERWISE DISCLOSED WITHOUT WRITTEN CONSENT OF THE COMPANY
 POLAMCO LTD	
WESTON LOCK LOWER BRISTOL ROAD BATH BA2 1EP	