


REVISION			
LTR	DESCRIPTION	DATE	INITIAL
AA	ORIGINAL	9-5-03	SWJ



Parameter	Performance
Model Number	PC904N
Frequency	896-980 MHz
Gain	6dBd
Polarization	Vertical
VSWR	1.5:1 Nominal
E-Plane 3 dB Beamwidth	70°
H-Plane 3 dB Beamwidth	100°
Front to Back Ratio	15dB
RF Connector	N (female)
Power	200W
Weight	1.12 lbs

MATERIAL:	DRAWN S JOHNSON	DATE 9-5-03	CUSHCRAFT 48 PERIMETER ROAD MANCHESTER NH. 03108		
	ENGINEER R LITTLEFIELD	DATE 9-5-03			
DO NOT SCALE DRAWING	ENGINEERING MGR A ALEVY	DATE 9-5-03	TITLE: PC904N MOUNTING & OUTLINE		
UNLESS OTHERWISE SPECIFIED TOLERANCES ARE:	FINISH:				
			SCALE 1:2	SIZE B	SHEET 1 OF 1