SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 VDE APPROVED: EN 60939-2

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 6 AMP, 120/250 VAC, 6 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND: 0.25nA @ 120V 60Hz 0.50nA @ 250V 50Hz

DPERATING AMBIENT TEMP. RANGE: -10°C TD +40°C @ RATED CURRENT, $\rm I_r.$ IN AN AMBIENT, $\rm T_0$, HIGHER THAN 40°C, THE MAXIMUM DPERATING CURRENT, $\rm I_0$, IS AS FOLLOWS: $\rm I_0 = \rm I_r - \sqrt{\frac{85-T_0}{2}}$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES Ir FOR 8 SECONDS

CUSTOM	IER	DRAWING							
CATALOG # PMOOODZ6C									
ECN #	APP	RVD.	DATE						
ECN # 22-185505	JB		30N0V22						

TEST SPECIFICATIONS:

INDUCTANCE: 6.2 mH NDMINAL

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: 0.006µF ±20% LINE TO LINE: 2.0µF ±20%

DISCHARGE RESISTOR: 165K \(\infty \)

L/G AND L/L I.R.

ND DISCHARGE RESISTOR: 6000M (MIN.) @ 100VDC,

20°C AND 50% RH


RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500VAC OR 2250VDC FOR 1 MINUTE

LINE TO LINE: 1450VDC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50A-50A(MINIMUM) INSERTION LOSS					NOITS	1 FD2:	2	THIRD ANGLE			
FREQUENCY MHz	.01	. 05	. 10	. 15	.50	1.0	5.0	10.0	30.0	PROJECTION UNLESS OTHERWISE SPECIFIED,	Tyco Electronics CDRCIDM PRIDUCTS, 620 S. BUTTERFIELD RD. MANDELEIN IL 60060
COMMON dB	8	21	27	30	37	43	49	52	42	TOLERANCE TO BE ±.025 MATERIAL & FINISH: AS SUPPLIED THIS INFERNATION IS CONFIDENTIAL AND PROPRIETARY ID- THIS INFERNATION IS CONFIDENTIAL AND PROPRIETARY FOR THE PROPRIETARY FOR THE PROPRIETARY FOR THE PROPRIETARY FOR	POWER LINE FILTER TYCO ELECTRONICS PART NO. 2-1609109-7
DIFF. dB	10	15	34	44	75	75	75	70		IYCO ELECTRONICS CORPORATION AND ITS VORLOUTCE SUBSIDIARIES AND AFFILIARES. IT MAY NOT BE DISCLUSED IT ANYONE OTHER THAN TYCO ELECTRONICS PERSONEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA USA	SCALE: NTS DATE: 28MAYOB PMOOODZ6C C