#### SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REGUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECDGNIZED: UL 1283 VDE APPROVED: EN 60939-2

### OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 10 AMP, 120/250 VAC,

10 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

0.25mA @ 120V 60Hz EACH LINE TO GROUND: 0.50mA @ 250V 50Hz

DPERATING AMBIENT TEMP. RANGE: -10°C TD +40°C @ RATED CURRENT, In. IN AN AMBIENT,  $T_0$ , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT,  $I_0$ , IS AS FOLLOWS:  $I_0 = I_0 - \sqrt{85 - T_0}$ 

 $I_0 = I_r - \sqrt{85 - \overline{I_0}}$ 

# RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT DVERLDAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOM	IER DR.	AWING		
CATALOG # PMOSODZXC				
ECN #	APPRVD.	DATE		
ECN # 22-185505	JB	30N0V22		

# TEST SPECIFICATIONS:

INDUCTANCE: 4.0 mH NDMINAL

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: LINE TO LINE: 0.006µF ±20% 2.0µF ±20%

DISCHARGE RESISTOR: L/G AND L/L I.R.

ND DISCHARGE RESISTOR: 6000M₁ (MIN.) @ 100VDC,

20°C AND 50% RH


### RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500VAC DR 2250VDC FDR 1 MINUTE

LINE TO LINE: 1450VDC FDR 1 MINUTE

### FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50A-50A(MINIMUM) INSERTION LOSS					2				
FREQUENCY MHz	. 01	. 05	. 10	. 15	.50	1.0	5.0	10.0	30.0
CDMMDN dB	5	17	22	24	27	32	52	47	40
DIFF. dB	10	20	20	35	67	75	75	70	60

THIRD ANGLE PROJECTION			
UNLESS OTHER TOLERANCE TI MATERIAL & F	] BE ±.0	25	IED
THIS INFORMATION IS CONF			

<b>Tyco Electroni</b>	CS	5
DRCDM PRODUCTS, 620 S. BUTTERETELD RD. MUNDELET		

POWER LINE FILTER

REV.

 $\mathbb{C}$ 

MATERIAL & FINISH: AS SUPPLIED	PU"		NE LIFIE
THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO	TYCD ELECTRON		3-1609109-3
TYCO ELECTRONICS CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLUSED TO ANYONE OTHER THAY TYCO ELECTRONICS PERSONEL. WITHOUT WRITTEN AUTHORIZATION	SCALE: NTS	DATE: 28MAY08	CATALOG NO.
FROM TYCO ELECTRONICS CORPORATION. HARRISBURG, PENNSYLVANIA USA	DRW. BY: SD	DRIG: ELC	PMOSODZXC