



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	16MAY2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

PART NO	AS SUPPLIED		AS RECOVERED							
	MINIMUM EXPANDED I.D. (D)		JACKET & LINER DIA (H)		MAXIMUM RECOVERED JACKET I.D. (d)		MINIMUM RECOVERED JACKET WALL (W)		MINIMUM RECOVERED TOTAL WALL (L)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
QSZH-125-NR1	5.75	0.226	1.25	0.049	2.65	0.104	0.60	0.024	1.10	0.043
QSZH-125-NR2	7.50	0.295	1.65	0.065	3.45	0.136	0.70	0.028	1.40	0.055
QSZH-125-NR3	11.00	0.433	2.40	0.094	4.65	0.183	0.80	0.031	1.80	0.071
QSZH-125-NR3A	14.00	0.551	3.00	0.118	5.90	0.232	0.90	0.035	2.15	0.085
QSZH-125-NR4	18.30	0.720	4.35	0.171	7.40	0.291	0.90	0.035	2.20	0.087

PRODUCT INFORMATION


- NON-FLAME RETARDANT
- OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN COLOUR: CLEAR
INNER LINER: THERMOPLASTIC HOT-MELT ADHESIVE COLOUR: BLACK
- SHRINK RATIO 4:1
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING
- DIMENSION H & L (JACKET & LINER) VALUE IS FOR REFERENCE ONLY

STANDARD CUTTING TOLERANCES (mm)

CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm (Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±0.1
- 2 PLC ±0.01
- 3 PLC ±0.001
- 4 PLC ±0.0001
- ANGLES ±
- FINISH -

DWN 16MAY2023
BASAVARAJA D A

CHK 16MAY2023
SELVAPANDIAN B

APVD 16MAY2023
MAYO BAKARE

PRODUCT SPEC
108-120002

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING



NAME
THERMOFIT QSZH-125 TUBING
DUAL WALL, HEAT-SHRINKABLE,
NON-FLAME RETARDED TUBING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - QSZH-125

SCALE NTS SHEET 1 OF 1 REV B