


REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	28APR2020	RK	HD

Component 1 RNF-3000-NR529


a) Part as supplied



b) Part fully recovered



Component 2 RBK-105-NR5030/A-X



PRODUCT DIMENSIONS & NOTES



DIMENSIONS (in millimetres)

Component 1: RNF-3000-NR529-0			Component 2: RBK-105-NR5030/A-X				
D	d	T	H	h	L	W1	W2
MIN	MAX	NOM	±20%	±20%	±20%	±20%	±30%
a	b	b					
15.0	4.0	0.9	8.55	6.50	2.75	12.25	1.0
Supplied cut length 40mm ±1.5mm			Supplied cut length 8mm ±0.8mm				
MATERIAL: JACKET: Flame Retarded Modified Polyolefin (Colour: Black)			MATERIAL: Hot Melt Adhesive (Colour: Amber)				

TE Connectivity. All Rights Reserved.

2015

©

DIMENSIONS:		DWN	04MAR2015	MATERIAL		FINISH			
mm		HD		-		-			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK	04MAR2015	<div>TE Connectivity</div>					
		APVD	04MAR2015						
		CD							
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		PRODUCT SPEC		NAME					
		108-120026							
		APPLICATION SPEC		-					
		-							
		WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
		1.06 g		A4	-	C-RBK-105-KIT-1103-A0	-		
		CUSTOMER DRAWING				SCALE	NTS	SHEET	1 of 1