



P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08JUN2023	BDA	MB

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

PART NO	AS SUPPLIED		AS RECOVERED							
	MINIMUM EXPANDED I.D. (D)		MAXIMUM RECOVERED I.D. REFERENCE ONLY (d)		MAXIMUM RECOVERED JACKET DIA (dl)		MINIMUM RECOVERED JACKET WALL (Wl)		MINIMUM RECOVERED TOTAL WALL REFERENCE ONLY (W)	
	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
RBK-VWS-125-NR1	5.70	0.224	1.27	0.050	2.65	0.104	0.80	0.031	1.42	0.056
RBK-VWS-125-NR2	8.00	0.315	1.65	0.065	3.01	0.119	1.06	0.042	1.78	0.070
RBK-VWS-125-NR3	10.80	0.425	2.40	0.094	4.55	0.179	1.16	0.046	2.14	0.084
RBK-VWS-125-NR4	17.78	0.700	4.45	0.175	7.40	0.291	1.04	0.041	2.41	0.095


PRODUCT INFORMATION

1. OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN TYPE COLOUR: CLEAR  
INNER LINER: POLYAMIDE HOT-MELT ADHESIVE COLOUR: LIGHT AMBER
2. SHRINK RATIO: 4:1
3. FULLY RECOVERED LONGITUDINAL SHRINKAGE 0 TO -10%
4. TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
mm(Inches)



MATERIAL  
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±
- 1 PLC ±0.1
- 2 PLC ±0.01
- 3 PLC ±0.001
- 4 PLC ±0.0001
- ANGLES ±
- FINISH -

DWN 08JUN2023  
BASAVARAJA D A

CHK 08JUN2023  
SELVAPANDIAN B

APVD 08JUN2023  
MAYO BAKARE

PRODUCT SPEC  
108-120001

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING



NAME  
RBK-VWS-125-X  
DUAL WALL HEAT SHRINKABLE NON FLAME  
RETARDED TUBING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - RBK-VWS-125-X -

SCALE NTS SHEET 1 OF 1 REV A