


| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|-----|-----------------|-----------|-----|------|
| | A | INITIAL RELEASE | 16MAY2023 | BDA | MB |
| | | | | | |
| | | | | | |

PART AS SUPPLIED



PART FULLY RECOVERED



PRODUCT DIMENSIONS

| SIZE | AS SUPPLIED | | AS RECOVERED | | | | | |
|------|---------------------------|-------|----------------------------|-------|---|-------------|---|-------------|
| | MINIMUM EXPANDED I.D. (D) | | MAXIMUM RECOVERED I.D. (d) | | TOTAL WALL THICKNESS AFTER RECOVERY (W) | | OUTER JACKET WALL THICKNESS AFTER RECOVERY (WI) | |
| | mm. | in. | mm. | in. | mm. | in. | mm. | in. |
| 4/1 | 4.00 | 0.157 | 1.00 | 0.039 | 0.80±0.15 | 0.031±0.006 | 0.50±0.12 | 0.020±0.005 |
| 8/2 | 8.00 | 0.315 | 2.00 | 0.079 | 0.90±0.20 | 0.035±0.008 | 0.60±0.12 | 0.024±0.005 |
| 12/3 | 12.00 | 0.472 | 3.00 | 0.118 | 1.20±0.25 | 0.047±0.010 | 0.80±0.15 | 0.031±0.006 |
| 16/4 | 16.00 | 0.630 | 4.00 | 0.157 | 1.50±0.25 | 0.059±0.010 | 1.00±0.20 | 0.039±0.008 |

PRODUCT INFORMATION


- NON-FLAME RETARDANT
- OUTER JACKET: IRRADIATED MODIFIED POLYOLEFIN COLOUR: CLEAR
INNER LINER: HOT MELT ADHESIVE COLOUR: LIGHT AMBER
OTHER COLOURS ARE POSSIBLE BY SPECIAL CONTRACT
- SHRINK RATIO: 4:1
- LONGITUDINAL CHANGE 0 TO -15%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES(mm)

| CUT LENGTH | TOLERANCE |
|-------------------|-----------|
| UPTO TO 9.90mm | ±1.50mm |
| 10mm TO 24.90mm | ±1.50mm |
| 25mm TO 54.90mm | ±1.50mm |
| 55mm TO 99.90mm | ±3.00mm |
| 100mm TO 149.90mm | ±4.00mm |
| 150mm TO 499.90mm | ±5.00mm |
| 500mm AND GREATER | ±25.40mm |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm(Inches)



MATERIAL
SEE NOTE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

| | |
|--------|---------|
| 0 PLC | ± |
| 1 PLC | ±0.1 |
| 2 PLC | ±0.01 |
| 3 PLC | ±0.001 |
| 4 PLC | ±0.0001 |
| ANGLES | ± |

FINISH

DWN 16MAY2023

BASAVARAJA D A

CHK 16MAY2023

SELVAPANDIAN B

APVD 16MAY2023

MAYO BAKARE

PRODUCT SPEC

RK-6214

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



NAME
RPPM STANDARD SIZES
DUAL WALL SLEEVING

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-RPPM -

SCALE NTS SHEET 1 OF 1 REV A