


REVISION			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE OF CD PER ECO-19-013153	9/18/2019	I. MYONG



NOTES:

1. FLEXIBLE, TWO PART MODIFIED EPOXY ADHESIVE.
2. TEMPERATURE RANGE: -55°C TO +135°C
3. BOXED KIT CONTENTS;

KIT A:

- 10 ADHESIVE SACHETS, 3g EACH.
- 10 MIXING CUPS
- 10 ABRASIVE PAPER SHEETS
- 10 MIXING STICKS
- 1 INSTALLATION PROCEDURE

4. SPECIFICATIONS:

Raychem RT-1009

5. SDS DOCUMENTS:

RAY 3003A  
RAY 3003B

6. SHELF LIFE:

REFER TO TE SPEC SHEET No. 126-116006.

Raychem Harness & Components **CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. AND INCH DIMENSIONS ARE IN SHOWN IN (PARENTHESES).							
DECIMALS: .000 ± 0.000 .00 ± 0.00 .0 ± 0.0	ANGLES: ± 0° 00'						
TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.		TITLE: TE/Raychem TWO-PART MODIFIED EPOXY ADHESIVE					
		DRAWING NO: <b>S1009</b>					
DRAWN: 21Jun2019 G.Rositano	APPROVED: 19JUL2019 I.Myong	CAGE CODE 06090	CAD FILE: S-1006-Kit-A_cd	SIZE: A	SCALE: 	THIRD ANGLE PROJ. 	SHEET: 1_OF_1