
	REVISION										
REV	DESCRIPTION	DATE	APPROVED								
A	INITIAL RELEASE OF CD PER ECO-19-013153	9/18/2019	I. MYONG								



NOTES:

- 1. ONE-PART EPOXY FLEXIBLE ADHESIVE TAPE.
- 2. TEMPERATURE RANGE: -55°C TO +200°C
- 3. TAPE IS SUPPLIED ON 100 FOOT REEL

3/4" WIDE X .020" THICK X 100FT

4. SPECIFICATIONS:

Raychem RT-1255 Raychem RT-1014

5. SDS DOCUMENTS:

RAY 3133

6. SHELF LIFE:

REFER TO TE SPEC SHEET No. 126-116006.

Raychem Harness & Components **CUSTOMER DRAWING**

	.000 ± DECIMALS: .00 ±	PECIFIED DIMENSIONS ARE ARE IN SHOWN IN (PARE) 0.000 0.000 ANGLES 0.0	N MILLIMETERS. ITHESES). : ± 0° 00'	=	TE		TE C	Connectivi	ty	
	THE RIGH DRAWING	TE CONNECTIVITY RESERVES THE RIGHT TO AMEND THIS DRAWING AT ANYTIME. USERS SHOULD EVALUATE THE			TTLE: TE/Raychem FLEXIBLE THERMOFIT ADHESIVE TAPE					
	SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION.			DRAWING NO: S1255-04						
ı.	DRAWN: 21Jun2019 G.Rositano	APPROVED: 19JUL2019 I.Myong	CAGE CODE 06090		cd	SIZE: A	SCALE:	THIRD ANGLE PROJ.	SHEET: 1_OF_1	
d.	SHOULD EVALUATE THE SUITABILITY OF THE PRODUCT FOR THEIR APPLICATION. DRAWN: 21Jun2019 APPROVED: 19JUL2019 CAGE CODE			DRAWING NO: \$1255-04 CAD FILE: SIZE: SCALE: THIRD ANGLE PROJ. SHEET:						

© 2019 TE Connectivity Corporation. All rights reserved