

2		1
45		
	CHANGED BY/DATE	APPROVED BY/DATE
	S.J. 10/29/10	S.J. 10/29/10

	Performance	
er	S2406BFNM	
е	Omnidirectional	
	2.4-2.5 GHz	
	8 dBi typical	
се	50 Ohm	
GHz)	1.7:1 Max.	
mwidth	Omnidirectional	
1	Linear Vertical	
wer	50 Watts	
or	Fixed N-Male	
	Upright or inverted	
	OMNIMT-HK Mast Mount Kit for	
lity	25mm to 54mm mast diameter	
	White UV Fiberglass	
al	200 kph	
	Operating: -30 to +70 C	
e temp.	Storage: -40 to +85 C	