


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	4/23/18	J.B	T.L

## Raychem SCL Heat - Shrinkable Tubing



**Table 1: Dimensions mm (inches)**

Size	Additional Standard Color	As Supplied		Fully Recovered									
		Inside Diameter Minimum (d)		Inside Diameter Maximum (D)		Total Wall thickness (W)						Inner Meltable Wall Thickness (W1)	
						Minimum		Maximum		Nominal		Nominal	
		mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.	mm.	in.
1/8	Brown	3.17	0.125	0.58	0.023	0.81	0.032	1.11	0.044	0.96	0.038	0.5	0.020
3/16	Gray	4.74	0.187	1.52	0.060	0.93	0.037	1.24	0.049	1.09	0.043	0.64	0.025
1/4	White	6.35	0.250	2.03	0.080	1.04	0.041	1.34	0.053	1.19	0.047	0.68	0.027
3/8	Red	9.93	0.375	3.42	0.135	1.09	0.043	1.44	0.057	1.27	0.050	0.76	0.030
1/2	Blue	12.70	0.500	4.95	0.195	1.21	0.048	1.57	0.062	1.39	0.055	0.88	0.035
3/4	Yellow	19.05	0.750	7.95	0.313	1.47	0.058	1.82	0.072	1.65	0.065	1.01	0.040
1	N/A	25.40	1.000	10.16	0.400	1.72	0.068	2.08	0.082	1.90	0.075	1.01	0.040

**Color:** Jacket and core colors are black and as indicated in the table. Additional colors available upon request.

Reference Specification TEC-108-120027

THIS DRAWING IS UNPUBLISHED. ALL RIGHTS RESERVED. © COPYRIGHT 2018 TE Connectivity

DIMENSIONS: INCHES	DWN J. Bitter	01JAN2018	MATERIAL	-	FINISH	-	
	CHK T. Licko	-	TE Connectivity				
TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD T. Licko	-					
0 PLC ± -	PRODUCT SPEC	-	NAME Raychem SCL Heat-Shrinkable Tubing				
1 PLC ± -	APPLICATION SPEC	-					
2 PLC ± -	WEIGHT	-	SIZE	A4	CAGE CODE	06090	
3 PLC ± -		-	DRAWING NO	C=SCL		RESTRICTED TO	-
4 PLC ± -			CUSTOMER DRAWING	SCALE	None	SHEET	1 OF 1
ANGLES ± -							