
CUSTOMER DRAWING



Product		Pro	duct Dimens	ions	Cable Dimensions				
Name	Ident.	L±1.75	øΑ	øΒ	øС	øD	øΕ	øF	øG
	Code	(L±0.07)	min	min	min	max	max	min	min
ST18-1-00	ST181R	16.5	1.90	2.65	8.25	1.90	2.65	0.90	0.50
		(0.650)	(0.075)	(0.105)	(0.325)	(0.075)	(0.105)	(0.035)	(0.020)
ST18-2-00	ST182R	16.5	2.65	3.68	8.25	2.65	3.68	1.40	0.72
		(0.650)	(0.105)	(0.145)	(0.325)	(0.105)	(0.145)	(0.055)	(0.030)
ST18-3-00	ST183R	16.5	4.30	5.08	8.25	4.30	5.08	2.15	1.25
		(0.650)	(0.170)	(0.200)	(0.325)	(0.170)	(0.200)	(0.085)	(0.050)
ST18-4-00	ST184R	19.1	5.95	6.45	8.25	5.95	6.45	3.30	1.80
		(0.750)	(0.235)	(0.255)	(0.325)	(0.235)	(0.255)	(0.130)	(0.070)
ST18-5-00	ST185R	19.1	7.00	7.60	8.25	7.00	7.60	4.30	2.50
		(0.750)	(0.275)	(0.300)	(0.325)	(0.275)	(0.300)	(0.170)	(0.100)

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene fluoride.
- 2. SOLDER PREFORM WITH FLUX:

SOLDER: TYPE Cd18 per ANSI-J-STD-006.


FLUX: TYPE ROL0 per ANSI-J-STD-004.

3. MELTABLE RINGS: Stabilized thermoplastic. Color: blue.

APPLICATION

- 1. These parts are designed to provide an environment protected shield terminations on cables, rated for 105°C minimum, meeting the dimensional criteria listed, having tin or silver plated shields.
- 2. When installed per Raychem process standard RCPS-100-70, assemblies will meet requirements of Raychem Specification RT-1404
- 3. Temperature range: -55°C to +125°C.

For best results, prepare the cable as shown:



TE Connectivity, TE connectivity (logo), Raychem, Thermofit, and SolderSleeve are trademarks

Raychem THERMOF DEVICES			FIT	SOLDERSLEEVE SHIELD TERMINATOR, LOW TEMPERATURE					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.					DOCUMENT NO.: ST18-X-00				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: I ROUGHNE MICRON	this drawing at any tim evaluate the suitability			Revision: 6		Issue Date: March 2020		
DRAWN BY: DATE: M. FORONDA 03/22/99		E: 03/22/99	ECO: ECO-20-003568		SCALE: None	SIZE: A	SHEET: 1 of 1		