



TYPE 1: SIDE ENTRY

类型 1: 侧出





NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE: POWDER COATED, GREY
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
表面处理: 粉末涂层, 灰色
防护等级: IP65 (配合)

TYPE 2: TOP ENTRY, OTHER SPEC REFER TO TYPE 1

类型 2: 顶出, 其他规格参考类型 1.



T1243240140-000	H24B-XHTG-M40	H24B HOOD, TOP ENTRY M40, H109.5, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M40, H109.5, 4耳, 高结构, 灰色粉末喷涂	-	M40	TYPE 2 类型 2
T1243240150-000	H24B-XHTG-M50	H24B HOOD, TOP ENTRY M50, H109.5, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 顶出M50, H109.5, 4耳, 高结构, 灰色粉末喷涂	-	M50	
T1233240140-000	H24B-XHTS-M40	H24B HOOD, SIDE ENTRY M40, H109.5, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出M40, H109.5, 4耳, 高结构, 灰色粉末喷涂	M40	-	TYPE 1 类型 1
T1233240150-000	H24B-XHTS-M50	H24B HOOD, SIDE ENTRY M50, H109.5, 4 EAR, HIGH CONSTRUCTION, POWDER COATED, GREY H24B上壳, 侧出M50, H109.5, 4耳, 高结构, 灰色粉末喷涂	M50	-	
PART NUMBER 料号	DESCRIPTION 描述		IG1	IG2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 10JAN2019 WENQING RAO	TE Connectivity			
DIMENSIONS: mm		CHK 10JAN2019 GINO YAO				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH		APVD 10JAN2019 CHRIS WANG	NAME H24B-XHTS/TG-M50			
MATERIAL -		PRODUCT SPEC 108-137013	SIZE A2	CAGE CODE -	DRAWING NO C-T12X3240150000	RESTRICTED TO -
-		APPLICATION SPEC 114-137013	WEIGHT -		CUSTOMER DRAWING	
		SCALE 3:5		SHEET 1 OF 1	REV B1	