






REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A I	ECR-19-002408	19MAR2019	RG	CW
	B	ECR-20-007762	23NOV2020	BS	CW
	B I	ECR-22-148038	8AUG2022	RG	CW
	C	ECR-25-244452	23JUN2025	WQR	RB




SECTION A - A
SCALE 3:2




- NOTES:
- TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ZINC ALLOY
SURFACE TREATMENT: POWDER-COATED, GRAY
DEGREE OF PROTECTION: IP65 (MATED)
 - RESTRICTED MATING HOUSING: T1509034000-000
- 注释:
- 技术参数:
主体材料: 锌合金
表面处理: 粉末喷涂, 灰色
防护等级: IP65 (配合)
 - 限定互配下壳: T1509034000-000




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROBERT GAN 26DEC2018	 TE Connectivity H3A-MTS-PG/M FOR CROSS MATING					
DIMENSIONS: mm		CHK GINO YAO 26DEC2018						
		APVD CHRIS WANG 26DEC2018						
		PRODUCT SPEC 108-137012						
MATERIAL - -	FINISH - -	APPLICATION SPEC 114-137012	SIZE A3	CAGE CODE -	DRAWING NO C-T13190321XX000	RESTRICTED TO -		
		WEIGHT -						
CUSTOMER DRAWING					SCALE 1:1	SHEET 1	OF 2	REV C

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	20
© COPYRIGHT 20		BY -	ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-




TYPE 1
类型 1
WITH TE LOGO
TE 标识



TYPE 2
类型 2
NO LOGO
无标识

T1319032120-001	H3A-MTS-M20	H3A HOOD,SIDE ENTRY M20,2 EAR, NO LOGO,POWDER COATED,GREY H3A上壳,侧出M20,2耳,无标识,灰色粉末喷涂	M20X1.5	TYPE 2 类型 2
T1319032111-000	H3A-MTS-PG11	H3A HOOD,SIDE ENTRY PG11,2 EAR, POWDER COATED,GREY H3A上壳,侧出PG11,2耳,灰色粉末喷涂	PG11	TYPE 1 类型 1
T1319032120-000	H3A-MTS-M20	H3A HOOD,SIDE ENTRY M20,2 EAR, POWDER COATED,GREY H3A上壳,侧出M20,2耳,灰色粉末喷涂	M20X1.5	
PART NUMBER 料 号		PART DESCRIPTION 描 述	THREAD 螺纹	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROBERT GAN 26DEC2018	 TE Connectivity		
		CHK GINO YAO 26DEC2018			
DIMENSIONS: mm		APVD CHRIS WANG 26DEC2018	NAME H3A-MTS-PG/M FOR CROSS MATING		
		PRODUCT SPEC 108-137012			
		APPLICATION SPEC 114-137012			
MATERIAL -		WEIGHT -	SIZE A3	CAGE CODE -	DRAWING NO C-T13190321XX000
FINISH -		CUSTOMER DRAWING		SCALE 1:1	SHEET 2 OF 2
				RESTRICTED TO -	REV C