





| REVISIONS |     |               |           |     |      |
|-----------|-----|---------------|-----------|-----|------|
| P         | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|           | A   | INITIAL       | 14JUL2018 | KW  | CW   |
|           | B   | ECR-21-108563 | 30JUL2021 | WQR | CW   |
|           |     |               |           |     |      |
|           |     |               |           |     |      |




NOTES:  
I. TECHNICAL CHARACTERISTICS:  
HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY  
HOUSING SURFACE: CONDUCTIVE PAINTING  
HOUSING SURFACE COLOR: TRANSPARENCY  
HOUSING RESISTANCE:  $\leq 10 \text{ m}\Omega$   
SEAL MATERIAL: CONDUCTIVE NBR  
DEGREE OF PROTECTION: IP65 (MATED)

注釋：  
1. 技術參數：  
下殼材料： 鋁合金  
下殼表面處理： 噴導電漆  
下殼表面處理顏色： 透明  
下殼電阻：  $\leq 10\ \Omega$   
密封圈材料： 導電NBR  
防護等級： IP65（配合）



PANEL CUT OUT  
面板开口尺寸



|                    |                         |                                                                                                 |
|--------------------|-------------------------|-------------------------------------------------------------------------------------------------|
| T1415243000-000    | H24B-AGS-EMC            | H24B EMC HOUSING, BULKHEAD MOUNTED,<br>STAINLESS STEEL DOUBLE LOCKING<br>H24B 屏蔽下壳, 开孔安装, 不锈钢双扣 |
| PART NUMBER<br>料 号 | PART DESCRIPTION<br>描 述 |                                                                                                 |

|                                                                                       |  |                                                                                                                                                          |  |                                                                                                       |  |
|---------------------------------------------------------------------------------------|--|----------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------|--|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |  | DWN 14JUL2018<br>KAYLA WANG<br>CHK 14JUL2018<br>GINO YAO<br>APVD 14JUL2018<br>CHRIS WANG<br>PRODUCT SPEC<br>108-137013<br>APPLICATION SPEC<br>114-137013 |  |  TE Connectivity |  |
| DIMENSIONS:<br>mm                                                                     |  | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ±.<br>1 PLC ±.<br>2 PLC ±.<br>3 PLC ±.<br>4 PLC ±.<br>ANGLES ±.<br>FINISH                                |  | NAME<br>H24B-AGS-EMC                                                                                  |  |
|  |  | WEIGHT<br>-                                                                                                                                              |  | SIZE<br>A2                                                                                            |  |
| MATERIAL<br>-<br>-                                                                    |  | CUSTOMER DRAWING                                                                                                                                         |  | CAGE CODE<br>00779                                                                                    |  |
|                                                                                       |  |                                                                                                                                                          |  | DRAWING NO<br>C-T1415243000000                                                                        |  |
|                                                                                       |  |                                                                                                                                                          |  | RESTRICTED TO<br>-                                                                                    |  |
|                                                                                       |  |                                                                                                                                                          |  | SCALE<br>1:1                                                                                          |  |
|                                                                                       |  |                                                                                                                                                          |  | SHEET<br>1 OF 1                                                                                       |  |
|                                                                                       |  |                                                                                                                                                          |  | REV<br>B                                                                                              |  |