

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	03JUN2015	DL	CW
	AI	ECR-17-017115	30NOV2017	CH	CW
	B	ECR-21-109004	16AUG2021	WQR	CW

4X $\varnothing 5.50$

8X M3 THREAD
8X M3 螺纹孔

2X 65.00

2X 27.00

2X 9.20

4X 77.50

2X 110.00

82.50

(86.0)

NOTES:

1. TECHNICAL CHARACTERISTICS:
 BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
 SURFACE TREATMENT: POWDER COATED, GREY
 DEGREE OF PROTECTION: IP65 (MATED)

注释:

1. 技术参数:
 主体材料: 铝合金
 表面处理: 灰色粉末喷涂
 防护等级: IP65(配合)

4X $\varnothing 5.40$

86.00

2X 65.00

71.00

2X 110.00

开孔安装示意图
 PANNEL CUT OUT

SCALE 1:2

T1500322000-000	H32B-AG-LB	H32B HOUSING, BULKHEAD MOUNTED, STAINLESS STEEL SINGLE LOCKING, POWDER COATED, GREY H32B下壳, 开孔安装, 不锈钢单扣, 灰色粉末喷涂
PART NUMBER 料号	PART DESCRIPTION 描述	

94.00

(97.6)

(37.6)

(6.5)

(110.6)

(127.5)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-
FINISH	-

MATERIAL

-

DWN 03JUN2015

DAVID.LI

CHK 03JUN2015

CHRIS.WANG

APVD 03JUN2015

XIANG.XU

PRODUCT SPEC

108-137013

APPLICATION SPEC

114-137013

WEIGHT

-

CUSTOMER DRAWING

NAME

H32B-AG-LB

SIZE

A3

CAGE CODE

-

DRAWING NO

C-T1500322000000

RESTRICTED TO

-

TE Connectivity

SCALE 4:5

SHEET 1 OF 1

REV B

1470-19 (3/13)