

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS




P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	05JUL2017	DW	CW
	B	ECR-20-014388	26NOV2020	WQR	CW

NOTES:

1. TECHNICAL CHARACTERISTICS:
HOUSING MATERIAL: DIE CAST ALUMINIUM ALLOY
HOUSING SURFACE: CONDUCTIVE PAINTING
HOUSING SURFACE COLOR: TRANSPARENCY
HOUSING RESISTANCE: ≤10 mΩ
SEAL MATERIAL: CONDUCTIVE NBR
DEGREE OF PROTECTION: IP65 (MATED)


注释:

1. 技术参数:
下壳材料: 铝合金
下壳表面处理: 喷导电漆
下壳表面处理颜色: 透明
下壳电阻: ≤10 mΩ
密封圈材料: 导电NBR
防护等级: IP65(配合)




SCALE 1:2

PANEL CUT OUT DIMENSION, ONLY FOR REFERENCE
面板开口尺寸, 仅供参考



TI505102000-000	H10B-AGS-LB-EMC	H10B EMC HOUSING,BULKHEAD MOUNTED, STAINLESS STEEL SINGLE LOCKING H10B 屏蔽下壳, 开孔安装, 不锈钢单扣
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID WANG 05JUL2017	 TE Connectivity				
		CHK GINO YAO 05JUL2017					
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-	APVD CHRIS WANG 05JUL2017	NAME H10B-AGS-LB-EMC				
		PRODUCT SPEC 108-137016					
MATERIAL -		APPLICATION SPEC 114-137016	SIZE A3	CAGE CODE 00779	DRAWING NO C-T1505102000000	RESTRICTED TO -	
-		FINISH -	WEIGHT -				
Customer Drawing			SCALE 1:1	SHEET 1 OF 1	REV B		