

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.








REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	ECR-19-002408	19MAR2019	RG	CW
	B	ECR-20-007782	24NOV2020	BS	CW
	C	ECR-23-182522	27JUL2023	DW	CW
	D	ECR-25-244452	26JUN2025	WQR	RB

- NOTES:
1. TECHNICAL CHARACTERISTICS:
HOUSING MATERIAL: DIE CAST ZINC ALLOY
SURFACE: POWDER COATED, RAL7037
SEAL MATERIAL: NBR
DEGREE OF PROTECTION: IP65 (MATED)
2. RESTRICTED MATING HOOD:
SIDE ENTRY: T1319032111-000, T1319032120-000
TOP ENTRY: T1329032111-000, T1329032120-000


- 注释:
1. 技术参数:
下壳材料: 锌合金
表面处理: 粉末涂层, RAL7037
密封材料: NBR
防护等级: IP65(配合)

2. 限定互配上壳: :
侧出上壳: T1319032111-000, T1319032120-000
顶出上壳: T1329032111-000, T1329032120-000



PANEL CUT OUT

T1509034000-000	H3A-MAG	H3A HOUSING, BULKHEAD MOUNTED, METAL SINGLE LOCKING, POWDER COATED, GREY H3A下壳, 开孔安装, 金属单扣, 灰色粉末喷涂
PART NUMBER 料号	PART DESCRIPTION 描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROBERT GAN 9NOV2018	 TE Connectivity		
		CHK GINO YAO 9NOV2018			
		APVD CHRIS WANG 9NOV2018			
		PRODUCT SPEC 108-137012			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APPLICATION SPEC 114-137012	NAME H3A-MAG FOR CROSS MATING		
	0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH	WEIGHT -	SIZE A3	CAGE CODE 00779	DRAWING NO T1509034000000
MATERIAL -	-	CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1	RESTRICTED TO -
				REV D	