

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	08JUL2015	DL	CW
	B	ECR-20-008181	16JUL2020	WQR	CW

43  
27  
57  
73  
88.7  
92.6  
4-M3

56.6  
88.7  
117.5

20  
PG/M

NOTES:

1. TECHNICAL CHARACTERISTICS:  
 BODY MATERIAL: DIE CAST ALUMINIUM ALLOY  
 SURFACE TREATMENT: POWDER-COATED, GRAY  
 DEGREE OF PROTECTION: IP65 (MATED)

注释:

1. 技术参数:  
 主体材料: 铝合金  
 表面处理: 粉末喷涂, 灰色  
 防护等级: IP65(配合)

94  
82  
52  
40  
4-Ø5.5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
	0 PLC ±-
	1 PLC ±-
	2 PLC ±-
	3 PLC ±-
	4 PLC ±-
	ANGLES ±-
	FINISH ±-
MATERIAL	
-	-
-	-

DWN	DAVID LI	08JUL2015
CHK	CHRIS WANG	08JUL2015
APVD	XU XIANG	08JUL2015
PRODUCT SPEC	108-137013	
APPLICATION SPEC	114-137013	
WEIGHT	-	
CUSTOMER DRAWING		

TI620102125-000		H10B-SDRS-LB-M25	M25
ASSEMBLY PART NUMBER		ASSEMBLY PART DESCRIPTION	PG/M
<b>STE</b> TE Connectivity			
NAME H10B-SDRS-LB-M25			
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-TI620102125000	
SCALE 3:5		SHEET 1 OF 1	REV B

1470-19 (3/13)