




TYPE 2

SCALE 3:5

WITH TE LOGO

SCALE 3:5

4X M3 THREAD HOLE
4X M3 螺纹孔

57

27

Technical drawing of a mechanical part, likely a bracket or support, showing a side view with dimensions. The part has a central circular feature with a crosshair. Dimensions include a total height of 75.3, a base height of 20, and a base width of 52. A small detail view of a hole is shown in the top right corner.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 27NOV2017 QIANG YUAN CHK 27NOV2017 GINO YAO APVD 27NOV2017 CHRIS WANG		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		NAME H10B-SDRMS-LB-PG/M	
		PRODUCT SPEC 108-137013 APPLICATION SPEC 114-137013		SIZE A2	
MATERIAL - -		WEIGHT -		CAGE CODE 00779	
FINISH - -		CUSTOMER DRAWING		DRAWING NO C-T1620102XXX001	
		SCALE 4:5		SHEET 2 OF 3	
				REV B	

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:
SEE SHEET 1

T1620102420-000	H10B-SDRMS-LB-2M20	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,2M20,METAL PROTECTION COVER,POWDER COATED,GREY H10B下壳,表面安装,不锈钢单扣,2M20,带金属保护盖,灰色粉末喷涂	M25X1.5	M25X1.5	TYPE-3: 2 ENTRY HOLE,WITH LOGO 类 型-2: 2个出线孔,TE LOGO
T1620102421-001	H10B-SDRMS-LB-2PG21	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,2PG21,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,2PG21,带金属保护盖,深灰色粉末喷涂,无LOGO	PG21	PG21	TYPE-2: 2 ENTRY HOLE,NO LOGO 类 型-2: 2个出线孔,无LOGO
T1620102416-001	H10B-SDRMS-LB-2PG16	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,2PG16,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,2PG16,带金属保护盖,深灰色粉末喷涂,无LOGO	PG16	PG16	
T1620102425-001	H10B-SDRMS-LB-2M25	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,2M25,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,2M25,带金属保护盖,深灰色粉末喷涂,无LOGO	M25X1.5	M25X1.5	
T1620102420-001	H10B-SDRMS-LB-2M20	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,2M20,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,2M20,带金属保护盖,深灰色粉末喷涂,无LOGO	M20X1.5	M20X1.5	TYPE-1: 1 ENTRY HOLE,NO LOGO 类 型-1: 1个出线孔,无LOGO
T1620102321-001	H10B-SDRMS-LB-PG21	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,PG21,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,PG21,带金属保护盖,深灰色粉末喷涂,无LOGO	PG21	-	
T1620102316-001	H10B-SDRMS-LB-PG16	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,PG16,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,PG16,带金属保护盖,深灰色粉末喷涂,无LOGO	PG16	-	
T1620102325-001	H10B-SDRMS-LB-M25	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,M25,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,M25,带金属保护盖,深灰色粉末喷涂,无LOGO	M25X1.5	-	
T1620102320-001	H10B-SDRMS-LB-M20	H10B HOUSING,SURFACE MOUNTED,STAINLESS STEEL SINGLE LOCKING,M20,METAL PROTECTION COVER,POWDER COATED,DEEP GREY,NO LOGO H10B下壳,表面安装,不锈钢单扣,M20,带金属保护盖,深灰色粉末喷涂,无LOGO	M20X1.5	-	
PART NUMBER 料 号	PART DESCRIPTION 描 述		PG/M THREAD-1 PG/M 螺纹孔-1	PG/M THREAD-2 PG/M 螺纹孔-2	TYPE 类 型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL
-
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -
-

DWN
QIANG YUAN 27NOV2017

CHK
GINO YAO 27NOV2017

APVD
CHRIS WANG 27NOV2017

PRODUCT SPEC
108-137013

APPLICATION SPEC
114-137013

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
H10B-SDRMS-LB-PG/M

SIZE
A2

CAGE CODE
00779

DRAWING NO
T1620102XXX001

RESTRICTED TO

SCALE
4:5

SHEET
3 OF 3

REV
B

1471-9 (3/13)