







TYPE 1

Single PG/M thread



TYPE 2

Two PG/M threads



All dimension is same as TYPE 1, except those defined in this TYPE
除了在本类型中定义的尺寸外, 其他尺寸同类型 I

NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: SEE TABLE
DEGREE OF PROTECTION: IP68 (MATED)

注释
1. 技术参数:
壳体材料: 铝合金
表面处理: 见表格
防护等级: IP68 (配合)

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
A		INITIAL RELEASE	08JUN2015	GY	CW
B		ECR-19-009256	02JUL2019	CD	CW
C		ECR-20-012069	08MAY2021	BS	CW

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN: Gino.Yao 08JUN2015	 TE Connectivity	
		CHK: Chris.Wong 08JUN2015		
		APVD: Xiang.Yu 08JUN2015		
		NAME: H10BPR-TGH-PG/M		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		
mm		0 PLC ±0.1		
		1 PLC ±0.1		
		2 PLC ±0.1		
		3 PLC ±0.1		
		4 PLC ±0.1		
		ANGLES ±0.1		
MATERIAL		FINISH		
-		-		
-		-		
		Customer Drawing		
		SCALE 1:1		
		SHEET 1 OF 2		
		REV C		

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

©

COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISONS

P	LYR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:
SEE SHEET 1
注释:
见 SHEET 1

T1920102220-000	H10BPR-TGH-2M20	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY 2M20,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出2M20,灰色粉末喷涂	M20	M20	-	TYPE 2 类型 2
T1920100225-000	H10BPR-TGH-2M25	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY 2M25,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出2M25,黑色粉末喷涂	M25	M25	-	
T1920100220-000	H10BPR-TGH-2M20	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY 2M20,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出2M20,黑色粉末喷涂	M20	M20	-	
T1920102132-000	H10BPR-TGH-M32	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M32,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出M32,灰色粉末喷涂	-	-	M32	TYPE 1 类型 1
T1920102129-000	H10BPR-TGH-PG29	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG29,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出PG29,灰色粉末喷涂	-	-	PG29	
T1920102125-000	H10BPR-TGH-M25	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M25,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出M25,灰色粉末喷涂	-	-	M25	
T1920102121-000	H10BPR-TGH-PG21	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG21,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出PG21,灰色粉末喷涂	-	-	PG21	
T1920102120-000	H10BPR-TGH-M20	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M20,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出M20,灰色粉末喷涂	-	-	M20	
T1920102116-000	H10BPR-TGH-PG16	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG16,POWDER COATED,GREY H10BPR上壳,对角锁定,顶出PG16,灰色粉末喷涂	-	-	PG16	
T1920101132-000	H10BPR-TGH-M32	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M40,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出M40,银白色粉末喷涂	-	-	M32	
T1920101129-000	H10BPR-TGH-PG29	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M32,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出M32,银白色粉末喷涂	-	-	PG29	
T1920101125-000	H10BPR-TGH-M25	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M25,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出M25,银白色粉末喷涂	-	-	M25	
T1920101121-000	H10BPR-TGH-PG21	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG21,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出PG21,银白色粉末喷涂	-	-	PG21	
T1920101120-000	H10BPR-TGH-M20	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M20,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出M20,银白色粉末喷涂	-	-	M20	
T1920101116-000	H10BPR-TGH-PG16	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG16,POWDER COATED,SILVER WHITE H10BPR上壳,对角锁定,顶出PG16,银白色粉末喷涂	-	-	PG16	
T1920100140-000	H10BPR-TGH-M40	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M40,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出M40,黑色粉末喷涂	-	-	M40	
T1920100132-000	H10BPR-TGH-M32	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M32,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出M32,黑色粉末喷涂	-	-	M32	
T1920100129-000	H10BPR-TGH-PG29	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG29,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出PG29,黑色粉末喷涂	-	-	PG29	
T1920100125-000	H10BPR-TGH-M25	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M25,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出M25,黑色粉末喷涂	-	-	M25	
T1920100121-000	H10BPR-TGH-PG21	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG21,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出PG21,黑色粉末喷涂	-	-	PG21	
T1920100120-000	H10BPR-TGH-M20	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY M20,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出M20,黑色粉末喷涂	-	-	M20	
T1920100116-000	H10BPR-TGH-PG16	H10BPR HOOD,DIAGONAL LOCKING,TOP ENTRY PG16,POWDER COATED,BLACK H10BPR上壳,对角锁定,顶出PG16,黑色粉末喷涂	-	-	PG16	
PART NUMBER 料 号	PART DESCRIPTION 描 述		PG/M THREAD-3 PG/M 螺纹-3	PG/M THREAD-2 PG/M 螺纹-2	PG/M THREAD-1 PG/M 螺纹-1	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
Gino.Yao

08JUN2015

CHK
Chris.Wong

08JUN2015

APVD
Kiang.Yu

08JUN2015

DIMENSIONS:

mm

0 PLC

1 PLC

2 PLC

3 PLC

4 PLC

ANGLES

±"

±"

±"

±"

±"

±"

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±"

FINISH

-

-

MATERIAL

-

-

Customer Drawing

SCALE 1:1

SHEET 2 OF 2

REV C

NAME
H10BPR-TGH-PG/M

SIZE
A1

CAGE CODE
-

DRAWING NO
T192010XXXXX00

RESTRICTED TO
-

TE Connectivity

4805 (13/13)