


TYPE 1: H6B EMC HOOD, SIDE ENTRY,
PLASTIC SINGLE LOCKING, HIGH CONSTRUCTION
H6B屏蔽上壳, 侧出, 塑料单扣, 高结构

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	10JUL2018	DW	CW
	B	ECR-20-007968	27SEP2020	WQR	CW



NOTES:
1. TECHNICAL CHARACTERISTICS:
HOOD MATERIAL: DIE CAST ALUMINIUM ALLOY
HOOD SURFACE: CONDUCTIVE PAINTING
HOOD SURFACE COLOR: TRANSPARENCY
HOOD RESISTANCE: $\leq 10\text{ m}\Omega$
DEGREE OF PROTECTION: IP65 (MATED)

注释:
1. 技术参数:
上壳材料: 铝合金
上壳表面处理: 喷导电漆
上壳表面处理颜色: 透明
上壳电阻: $\leq 10\text{ m}\Omega$
防护等级: IP65(配合)

TYPE 2: H6B EMC HOOD, TOP ENTRY,
PLASTIC SINGLE LOCKING, HIGH CONSTRUCTION
H6B屏蔽上壳, 顶出, 塑料单扣, 高结构



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 24FEB2018 DAVID WANG	 TE Connectivity			
		CHK 24FEB2018 GINO YAO				
		APVD 24FEB2018 CHRIS WANG	NAME H6B-TSBH/TGBH-SL-EMC-M/PG			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
mm				108-137016		
				APPLICATION SPEC		
				114-137016		
MATERIAL		FINISH		WEIGHT		
-		-		-		
				CUSTOMER DRAWING		
				SCALE 1:1		
				SHEET 1 OF 2		
				REV B		

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

NOTES:


SEE SHEET 1

T1B40065132-000	H6B-TGBH-SL-EMC-M32	H6B EMC HOOD,TOP ENTRY M32,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,顶出M32,塑料单扣,高结构	-	M32	TYPE 2 类型2
T1B40065125-000	H6B-TGBH-SL-EMC-M25	H6B EMC HOOD,TOP ENTRY M25,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,顶出M25,塑料单扣,高结构	-	M25	
T1B40065120-000	H6B-TGBH-SL-EMC-M20	H6B EMC HOOD,TOP ENTRY M20,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,顶出M20,塑料单扣,高结构	-	M20	
T1B30065132-000	H6B-TSBH-SL-EMC-M32	H6B EMC HOOD,SIDE ENTRY M32,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,侧出M32,塑料单扣,高结构	M32	-	TYPE 1 类型1
T1B30065125-000	H6B-TSBH-SL-EMC-M25	H6B EMC HOOD,SIDE ENTRY M25,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,侧出M25,塑料单扣,高结构	M25	-	
T1B30065120-000	H6B-TSBH-SL-EMC-M20	H6B EMC HOOD,SIDE ENTRY M20,PLASTIC SINGLE LOCKING,HIGH CONSTRUCTION H6B屏蔽上壳,侧出M20,塑料单扣,高结构	M20	-	
PART NUMBER 料 号	PART DESCRIPTION 描 述		PG/M THREAD-1 PG/M 螺纹孔-1	PG/M THREAD-2 PG/M 螺纹孔-2	TYPE 类型

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm



MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±-

1 PLC ±-

2 PLC ±-

3 PLC ±-

4 PLC ±-

ANGLES ±-

FINISH -

-

DWN 24FEB2018
DAVID WANG

CHK 24FEB2018
GINO YAO

APVD 24FEB2018
CHRIS WANG

PRODUCT SPEC
108-137016

APPLICATION SPEC
114-137016

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
H6B-TSBH/TGBH-SL-EMC-M/PG

SIZE
A2

CAGE CODE
00779

DRAWING NO
T1BX00651XX000

RESTRICTED TO
-

SCALE
1:1

SHEET
2

OF
2

REV
B

1471-9 (3/13)